

PRODUCT NUMBER
95615-XXXXLF

PLATING

- 0 = 0.20µm GOLD/GXT ON CONTACT AREA
2µm MIN MATTE TIN ON TAIL
- 1 = 0.76µm GOLD/GXT ON CONTACT AREA
2µm MIN MATTE TIN ON TAIL
- 3 = 0.38µm GOLD/GXT ON CONTACT AREA
2µm MIN MATTE TIN ON TAIL
- 5 = 0.38µm GXT FULL PLATED
- 6 = 0.76µm GXT FULL PLATED
- 7 = 0.76µm GOLD/GXT FULL PLATED
- 9 = 0.20µm GOLD/GXT FULL PLATED

1.27µm Ni MIN UNDERPLATING

NOTES:

1. MATERIAL HOUSING: HIGH TEMP. THERMOPLASTIC
UL 94V-0, COLOR CREAM
2. MATERIAL TERMINAL: COPPER ALLOY
3. TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW
4. 7N MIN. PIN RETENTION IN EITHER DIRECTION.
5. PACKAGING:

= POLYBAGS

T = TUBE AVAILABILITY : FROM 2x5 UP TO 2x 17

B = TUBE WITH PICK UP CAP AVAILABLE FROM 2x5 UP TO 2x 17

K = TAPE AND REEL WITHOUT PICK-UP CAP, AS AVAILABLE

A = TAPE AND REEL WITH LARGE PICK-UP CAP, AS AVAILABLE

TR = TAPE AND REEL WITH PICK-UP CAP, AS AVAILABLE.




6. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

- a - PLATING:
- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.
- b - MANUFACTURING PROCESS COMPATIBILITY
- THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C PEAK TEMPERATURE FOR 30 SECONDES
MAX IN A CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN.
- c - LABELLING:
- MEETS PACKAGING SPECS AS PER GS-14-920
- d - THIS PRODUCT MEETS EUROPEAN DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS DISCRIBED
IN GS-47-0004.



RoHS COMPATIBLE, SEE NOTE 6

PACKAGING, SEE NOTE 5


TOTAL NB OF POSITIONS, 08 TO 34



STANDARD PICK-UP CAP



LARGE PICK-UP CAP NOTE 5
NOT AVAILABLE FOR 2X2



mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO	projection 101	product family MINITEK HEADER	
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title	
T	F-23051	AMA	16.01.15	angles	.X ±0.3		SHR HEADER	
M	F07-0191	J.CO	07.09.05	linear	.XX ±0.13	scale 7:1	2.00mm SMT	
N	F08-0145	ELA	08.04.15	dr	JL.CORDIER 97.07.26	FCI	dwg no	
P	F11-0071	JCO	11.06.17	engr	J.COMPAGNON 97.07.26		sheet 1 of 1 size	
R	F11-0339	JCO	11.12.06	chr	JL.CORDIER 97.07.26		95615 A3	
S	B-19190	LMU	14.10.24	appo	J.COMPAGNON 97.07.26		type CUSTOMER Drawing	
sheet index	revision sheet							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[95615-010LF](#) [95615-016LF](#) [95615-112LF](#) [95615-120LF](#) [95615-130LF](#) [95615-134LF](#) [95615-008TR](#) [95615-014TR](#)
[95615-014TRLF](#) [95615-110TR](#) [95615-110TRLF](#) [95615-112TR](#) [95615-120TR](#) [95615-120TRLF](#) [95615-124TR](#)
[95615-124TRLF](#) [95615-008](#) [95615-112](#) [95615-120](#) [95615-130](#) [95615-928ALF](#) [95615-010TRLF](#) [95615-012TR](#)
[95615-012TRLF](#) [95615-018LF](#) [95615-020LF](#) [95615-024LF](#) [95615-024TRLF](#) [95615-026LF](#) [95615-028LF](#) [95615-](#)
[028TR](#) [95615-028TRLF](#) [95615-034K](#) [95615-034KLF](#) [95615-034LF](#) [95615-034TRLF](#) [95615-114TLF](#) [95615-116TR](#)
[95615-116TRLF](#) [95615-118LF](#) [95615-122LF](#) [95615-126LF](#) [95615-126TR](#) [95615-126TRLF](#) [95615-132LF](#) [95615-](#)
[314TLF](#) [95615-316TRLF](#) [95615-508LF](#) [95615-508TRLF](#) [95615-510LF](#) [95615-124](#) [95615-108LF](#) [95615-130TR](#)
[95615-124LF](#) [95615-116LF](#) [95615-010](#) [95615-116](#) [95615-030LF](#) [95615-012LF](#) [95615-108](#) [95615-114](#) [95615-](#)
[130TRLF](#) [95615-110LF](#) [95615-908LF](#) [95615-028ALF](#) [95615-710LF](#) [95615-114BLF](#) [95615-928TRLF](#) [95615-708LF](#)
[95615-516LF](#) [95615-112BLF](#) [95615-014ALF](#)