





08 CCM

Non-magnetic



Leaded Inductors / Medical Applications (Fixed Choke Coils)

Leaded Inductors / Medical Applications



Part No	Inductance	f_L	Tol	Q	f_Q	SRF	DCR	Rated DC
	L (μH)	(MHz)	\pm (%)	min	(MHz)	typ (MHz)	max (Ω)	Current max (mA)
08CCM-R47X-YY	0.47	1	10,20	65	25	400	0.060	2880
08CCM-R56X-YY	0.56	1	10,20	60	25	400	0.080	2160
08CCM-R68X-YY	0.68	1	10,20	60	25	350	0.100	1840
08CCM-R82X-YY	0.82	1	10,20	60	25	300	0.130	1540
08CCM-1R0X-YY	1.00	1	10,20	60	25	250	0.160	1280
08CCM-1R2X-YY	1.20	1	10,20	40	7.9	230	0.220	1080
08CCM-1R5X-YY	1.50	1	10,20	40	7.9	220	0.310	900
08CCM-1R8X-YY	1.80	1	10,20	40	7.9	200	0.350	850
08CCM-2R2X-YY	2.20	1	10,20	40	7.9	180	0.550	640
08CCM-2R7X-YY	2.70	1	10,20	40	7.9	160	0.650	625
08CCM-3R3X-YY	3.30	1	10,20	35	7.9	140	0.900	525
08CCM-3R9X-YY	3.90	1	10,20	35	7.9	130	1.200	475
08CCM-4R7X-YY	4.70	1	10,20	35	7.9	120	1.450	415

Core Material: Phenolic

Revision date: 09 Aug 2019

SPQ:

Packaging Form	Taped / Reel	Taped / Ammo pack
Axial	1200 [-01]	500 [-02]