



### Overview

|              |                                                                                                                                                                                                                                                                                                                                      |
|--------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Presentation | The Rack LCD Console with Integrated KVM Switch combines the functionality of Rack LCD Console and Analog KVM switches in one convenient package optimizing U space in the rack environment, eliminating cable clutter, and offering a value of two products functionality in one package. Keyboard is a US English keyboard layout. |
| Lead time    | Usually in Stock                                                                                                                                                                                                                                                                                                                     |

### Main

|                     |                                                                                                                                                                                |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Main Input Voltage  | 120 V<br>240 V                                                                                                                                                                 |
| Plug standard       | IEC 60320 C14                                                                                                                                                                  |
| Number of rack unit | 1U                                                                                                                                                                             |
| Cable length        | 6 ft (1.83 m)                                                                                                                                                                  |
| Number of cables    | 1                                                                                                                                                                              |
| Provided equipment  | USB KVM cable<br>Single user rack mount kit<br>PS2 KVM cable<br>NEMA 5-15 power cord<br>Installation guide<br>Firmware upgrade cable<br>Documentation CD<br>C13-C14 power cord |

### Physical

|                        |                      |
|------------------------|----------------------|
| Color                  | Black                |
| Height                 | 1.69 in (4.3 cm)     |
| Width                  | 19.02 in (48.3 cm)   |
| Depth                  | 27.99 in (71.1 cm)   |
| Net Weight             | 30.86 lb(US) (14 kg) |
| Mounting Location      | Front                |
| Mounting preference    | No preference        |
| Mounting Mode          | Rack-mounted         |
| Maximum Mounting Depth | 41.33 in (104.98 cm) |
| Minimum Mounting Depth | 26.77 in (68 cm)     |

### Input

|                 |          |
|-----------------|----------|
| Input Frequency | 50/60 Hz |
|-----------------|----------|

## Conformance

|                        |                                                                                            |
|------------------------|--------------------------------------------------------------------------------------------|
| Product Certifications | CUL Listed<br>C-tick<br>CE<br>Industry Canada<br>KCC<br>UL Listed<br>VDE<br>TAA compliance |
| Standards              | EN 60950<br>FCC Part 15 class A<br>IEC 60950                                               |

## Environmental

|                                       |                         |
|---------------------------------------|-------------------------|
| Ambient Air Temperature for Operation | 32...104 °F (0...40 °C) |
|---------------------------------------|-------------------------|

## Supported Hardware

|                |                                  |
|----------------|----------------------------------|
| Display colour | 16 colours                       |
| Display size   | 337.9 (H) x 270.3 (V)<br>17 inch |
| Trackball Type | PS/2 Touchpad<br>USB mouse       |
| Display Type   | LCD display                      |

## Ordering and shipping details

|                     |                         |
|---------------------|-------------------------|
| GTIN                | 731304278818            |
| Package weight(Lbs) | 44.40 lb(US) (20.14 kg) |

## Packing Units

|                  |                    |
|------------------|--------------------|
| Package 1 Height | 5.12 in (13 cm)    |
| Package 1 width  | 26.18 in (66.5 cm) |
| Package 1 Length | 32.68 in (83 cm)   |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                    |
|----------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                              |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           |  <a href="#">REACH Declaration</a>                                                                                                                              |
| REACH free of SVHC         | Yes                                                                                                                                                                                                                                                |
| EU RoHS Directive          | Compliant  <a href="#">EU RoHS Declaration</a>                                                                                                                  |
| Lead free                  | Yes                                                                                                                                                                                                                                                |
| Mercury free               | Yes                                                                                                                                                                                                                                                |
| RoHS exemption information |  Yes                                                                                                                                                            |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.                                                                                                                       |
| Take-back                  | Take-back program available                                                                                                                                                                                                                        |

## Contractual warranty

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|