




LENGTH $\pm T$





P1



P2

CABLE PRINTING: Amphenol Cables on Demand E119932-Y AWM 2464 80°C 300V
26AWG VW-1 LL84201 CSA AWM I/II A 80°C 300V 26AWG FT1 COPARTNER



NOTE:

- TESTING CONDITIONS:
 - INSULATION RESISTANCE: $10M\Omega$
 - VOLTAGE: DC300V/0.01S
 - CONDUCTOR RESISTANCE $2\Omega(\leq 3M)$, $5\Omega(>3M, <10M)$, $8M\geq 10\Omega$
- SHIELDING: COPPER FOIL TAPE COVER PREMOLD 360°,
DRAIN WIRE SOLDER TO CONNECTOR SHELL

PIN OUT

P1	P2	P1	P2
1	1 BLACK	9	9 GREY
2	2 BROWN	10	10 WHITE
3	3 RED	11	11 PINK
4	4 ORANGE	12	12 LIGHT GREEN
5	5 YELLOW	13	13 BLACK/WHITE
6	6 GREEN	14	14 BROWN/WHITE
7	7 BLUE	15	15 RED/WHITE
8	8 PURPLE	SHELL	SHELL DRAIN

NOTES: UNLESS OTHERWISE SPECIFIED



UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

DECIMALS
X $\pm X$
XX $\pm XX$
XXX $\pm XXX$

ANGLES
 $\pm X^\circ$

EAR NO.

APPROVALS

DATE

DRAWN

XF

CHECKED

HYJ

THIRD ANGLE PROJECTION

RESP ENG

MFG ENG

Amphenol Cables on Demand
20 VALLEY ST. ENDICOTT, NY 13760

DELUXE DB15M/M MOLDED

CAD FILE:

2

SIZE DWG. NO. CS-DSDMDB15MM-XXX

REV. A5

SCALE: N/A SHEET 1 OF 1