

Product: [Adapter Cable, RJ11/RJ45](#)



This adapter cable in conjunction with a Belden terminal cable with RJ45 connector allows a local connection from an external management station to the serial interface of a network device.

Product Description

Adapter Cable to convert from RJ45 8 pin to RJ11 6 pin. It can be applied with RJ45 to USB Terminal Cable: RJ11 – RJ45 (942 261-001) via 1:1 coupler to RJ45 – USB (942 096-001).

Technical Specifications

Product description

Type:	Adapter Cable RJ11/RJ45
Part Number:	942261001
Cable Length:	15 cm

Ambient conditions

Operating temperature:	0-+60 °C
Minimum Storage Temperature:	-20-+80 °C
Relative humidity (non-condensing):	10-95 %

Mechanical construction

Weight:	15 g
---------	------

Reliability

Guarantee:	24 months (please refer to the https://assets.belden.com/m/1424ddb7a3280e7a/original/Hirschmann-Automation-and-Control-GmbH-Terms-of-Guarantee.pdf terms of guarantee </a for detailed information)
------------	---

Scope of delivery and accessories

Scope of delivery:	Cable
--------------------	-------

Further Instructions

Product Documentation:	https://www.doc.hirschmann.com
Certificates:	https://www.doc.hirschmann.com/certificates.html

History

Update and Revision:	Revision Number: 0.90 Revision Date: 11-27-2025
----------------------	---

Variants

Item #	Type	Cable Length
942261001	ADAPTER Cable RJ11/RJ45	15 cm

Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.