



Product: [FI3B004RB](#) 

Indoor Riser OM3 Breakout 4F 2mm Sub-Units Aqua

Product Description

FX Indoor OM3 Breakout 4 Fibers OFNR Sub-Units (2.0MM) Aqua Jacket

Technical Specifications

Product Overview

Suitable Applications:	Horizontal Backbone
------------------------	---------------------

Fiber Specifications

Fiber Type:	OM3
Fiber Core Diameter:	50/125µm µm
Fiber Diameter:	250 µm
Fiber Buffer Material:	PVC - Polyvinyl Chloride
Fiber Buffer Diameter:	900 µm µm
Fiber Count:	4
Fiber Color Coding:	TIA-598-D

Cable Construction

Number of Active Subunits:	4
Fibers Per Subunit:	1
Subunit Diameter:	0.078 in (2.0 mm)
Fiber SubUnit Strength Members:	Aramid yarns
Central Strength Member Type:	GRP
Core Wrap Material:	Nomex Tape

Outer Jacket Specifications

Strength Member:	Aramid Yarns
Jacket Material:	PVC - Polyvinyl Chloride
Nom. Diameter:	0.321 in (8.2 mm)
Outer Jacket Color:	Aqua
Outer Jacket Ripcord:	2

Optical Characteristics

Wavelength	850 nm	1300 nm
Max. Attenuation	3.0 dB/km	1.0 dB/km
1 Gigabit Ethernet Performance	1000 m	550 m
10 Gigabit Ethernet Performance	300 m	--
Min. Effective Modal Bandwidth (EMB)	2000 MHz.km	--
Min. Overfilled Launch (OFL) Bandwidth	1500 MHz.km	500 MHz.km

Mechanical Characteristics

Minimum Bend Radius During Installation:	15x Cable OD
Minimum Bend Radius During Operation:	10x Cable OD
Max. Tensile Strength During Installation:	1330 N (300 lbf)

Max. Tensile Strength During Operation:	400 N (90 lbf)
Crush Resistance:	100 N/cm
Bulk Cable Weight:	17 lbs/kft (26 kg/km)

Temperature Range

Installation Temperature Range:	-10°C to +60°C
Operating Temperature Range:	-40°C to +70°C
Storage Temperature Range:	-40°C to +70°C

Standards and Compliance

Environmental Suitability:	Indoor
Sustainability:	CA Prop 65, Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Reaction to Fire:	OFNR, FT4
ICEA Compliance:	S-83-596
TIA/EIA Compliance:	ANSI/ICEA S-83-596

History

Update and Revision:	Revision Number: 0.69 Revision Date: 09-07-2025
----------------------	---

Part Numbers

Variants

Item #	Color	Putup Type	UPC
FI3B004RB	Aqua	Reel	612825369837

© 2026 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.