

Specification Sheet

Part Number: 156-01561

The "H" profile provides a broad surface contact to minimize the pinching of bundles.

Heavy duty fir tree mounts are equipped with a friction tab that will hold the tie in the mount, allowing them to be preassembled prior to installation.



Designed specifically for HellermannTyton 120 - 250 lb cable ties for heavy duty applications.

Article Number	156-01561
Type	T120ROSFT9CLG
Color	Black (BK)
Quantity Per	bag
Product Description	HellermannTyton Heavy Duty Fir Tree Mounts are designed with extreme applications in mind. They are optimized for up to 3-to-1 extraction versus insertion force to make assembly fast and easy. These mounts are sold as an assembly with a cable tie.
Short Description	2-Pc Cable Tie/Fir Tree Mount, 15" L, 0.35" (9mm) Hole, 120lb, PA66HS/PA66HIRHSUV, Black, 100/pkg

Global Part Name	T120ROSFT9CLG-PA66HS/PA66HIRHSUV-BK
------------------	-------------------------------------

Minimum Tensile Strength (Imperial)	120.0
-------------------------------------	-------

Minimum Tensile Strength (Metric)	535.0
-----------------------------------	-------

Length L (Imperial)	15.0
---------------------	------

Length L (Metric)	385.0
-------------------	-------

Fixation Method	Fir Tree
-----------------	----------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Outside Serrated
---------	------------------

Width W (Imperial)	0.30
--------------------	------

Width W (Metric)	7.6
------------------	-----

Bundle Diameter Min (Imperial)	0.20
--------------------------------	------

Bundle Diameter Min (Metric)	5.0
------------------------------	-----

Bundle Diameter Max (Imperial)	4.13
--------------------------------	------

Bundle Diameter Max (Metric)	105.0
------------------------------	-------

Thickness T (Imperial)	0.07
Thickness T (Metric)	1.8
Height H (Imperial)	1.16
Height H (Metric)	29.6
Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.5
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	12.7
Mounting Hole Diameter D (Imperial)	0.34 - 0.36
Mounting Hole Diameter D (Metric)	8.75 - 9.25 mm
Mounting Hole Diameter D Min (Imperial)	0.34
Mounting Hole Diameter D Max (Imperial)	0.36
Mounting Hole Diameter D Max (Metric)	9.25
Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HS PA66HIRHSUV

Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
--------------------	--

Flammability	UL 94 HB
--------------	----------

UV Resistant (Yes/No)	Yes
-----------------------	-----

Operating Temperature	-40°F to +221°F (-40°C to +105°C)
-----------------------	-----------------------------------

ROHS Compliant	Yes
----------------	-----

Package Quantity (Imperial)	100
-----------------------------	-----

Package Quantity (Metric)	100
---------------------------	-----

Customs Number	3926909988
----------------	------------