

Specification Sheet

Part Number: 156-03335



Capable of holding several cables, depending on cable tie size, for ultimate flexibility.

Zero-insertion-force design requires no tools for quick and easy mounting.

High impact modified, heat-resistant, UV stabilized material is ideal for long-term performance, even in extreme weather.

Cable Tie with Button Mount, 0.35" Hole Dia, 0.12" Max Panel, 0.07" Max Tie Width, PA66HIRHSUV, Black, 1000/ctn

Article Number	156-03335
Type	T50RUPBM9SET
Color	Black (BK)
Quantity Per	carton
Product Description	This button head mount includes a cable tie to secure cables and wire bundles to panels. Once placed through the panel hole, installers can insert the cable tie through the mount on the panel's opposite surface. The button head mount is designed to fit pre-stamped oval hole sizes 7x10mm, 7x12mm, 8.5x16mm, 9x12mm and 9x14mm with zero insertion force.
Short Description	Cable Tie with Button Mount, 0.35" Hole Dia, 0.12" Max Panel, 0.07" Max Tie Width, PA66HIRHSUV, Black, 1000/ctn

Global Part Name	T50RUPBM9SET-PA66HIRHSUV-BK
------------------	-----------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	8.0
---------------------	-----

Length L (Metric)	203.2
-------------------	-------

Fixation Method	Button Head
-----------------	-------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Width W (Imperial)	0.67
--------------------	------

Width W (Metric)	17.0
------------------	------

Bundle Diameter Min (Imperial)	0.16
--------------------------------	------

Bundle Diameter Min (Metric)	4.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.97
--------------------------------	------

Bundle Diameter Max (Metric)	50.0
------------------------------	------

Thickness T (Imperial)	0.05
------------------------	------

Thickness T (Metric)	1.2
Cable Tie Head Length (Imperial)	0.29
Cable Tie Head Width (Imperial)	0.30
Height H (Imperial)	0.53
Height H (Metric)	13.40
Panel Thickness Max (Imperial)	0.12
Panel Thickness Max (Metric)	3.0
Mounting Hole Diameter D (Imperial)	0.34 x 0.63 " 0.28 x 0.39 " 0.33 " 0.35 x 0.55 " 0.35 " 0.35 x 0.47 "
Mounting Hole Diameter D (Metric)	8.5 x 16.0 mm 9.0 x 12.0 mm 9.0 mm 7.0 x 10.0 mm 8.5 mm 9.0 x 14.0 mm
Mounting Hole Diameter D Min (Imperial)	0.28
Mounting Hole Diameter D Max (Imperial)	0.63
Mounting Hole Diameter D Max (Metric)	16.0

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
----------	--

Material Shortcut	PA66HIRHSUV
-------------------	-------------

Flammability	UL 94 HB
--------------	----------

Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)