

## Specification Sheet

Part Number: 156-03941

Pre-assembled 2-piece tie with arrowhead mount provides bundling and securing with one assembly.

TPE seal protects against ingress of water and debris.

Cable tie is outside serrated to reduce bundle chafing.

Low profile cable tie helps bundle wires neatly to accommodate wire harnesses with smaller diameters.

Low profile head won't snag on surrounding parts and wires.



Article Number 156-03941

Type LPT50RSRAH6.5SD

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton sealed arrowhead mount and tie are constructed of engineered nylon with a dual TPE (thermo plastic elastomer) seal. The combination of dual seal and engineered arrowhead provide superior sealing performance for applications where protection from moisture and debris is essential. Low profile cable tie features a compact, contoured head designed to use less space in confined areas and reduce protrusions that might otherwise interfere with or damage adjacent wire insulation and hoses. The outside serration provides a smooth inside surface to further minimize indentation or damage to soft bundles while offering high tensile strength and low insertion force. This mount is sold as an assembly with the cable tie.

Short Description	2-Pc Low Profile Cable Tie/Arrowhead w Seal, 0.6 - 1.1mm Panel, 6.5mm/6.35mm HEX, PA66HIRHSUV/TPE, BK, 500/bg
Global Part Name	LPT50RSRAH6.5SD-PA66HS/PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225.0
Length L (Imperial)	7.7
Length L (Metric)	194.6
Fixation Method	Arrowhead
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.20
Bundle Diameter Min (Metric)	5.0
Bundle Diameter Max (Imperial)	2.0

Bundle Diameter Max (Metric)	50.0
Height H (Imperial)	0.52
Height H (Metric)	13.25
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.08
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.04
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	1.1
Mounting Hole Diameter D (Imperial)	0.25 " (hexagonal) 0.25
Mounting Hole Diameter D (Metric)	6.5 mm 6.35 mm (hexagonal)
Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV PA66HS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
UV Resistant (Yes/No)	Yes

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) No

ROHS Compliant Yes

Package Quantity (Imperial) 500

Package Quantity (Metric) 500

Customs Number 3926909988

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)