

Gold Option	Gold Mouser Part Number	Cost-Optimized Alternative	Cost-Optimized Alternative Mouser Part Number
EHT-105-01-H-D	200-EHT-105-01-H-D	EHT-105-01-L-D	200-EHT10501LD
EHT-105-01-H-D-SM-P-TR	200-EHT-10501HDSMPTR	EHT-105-01-L-D-SM-P-TR	200-EHT10501LDSMPTR
EHT-105-01-S-D	200-EHT10501SD	EHT-105-01-L-D	200-EHT10501LD
EHT-105-01-S-D-RA	200-EHT10501SDRA	EHT-105-01-L-D-RA	200-EHT10501LDRA
EHT-105-01-S-D-SM	200-EHT10501SDSM	EHT-105-01-L-D-SM	200-EHT10501LDSM
EHT-105-01-S-D-SM-K-TR	200-EHT10501SDSMKTR	EHT-105-01-L-D-SM-K-TR	200-EHT10501LDSMKTR
EHT-105-01-S-D-SM-P-TR	200-EHT10501SDSMPTR	EHT-105-01-L-D-SM-P-TR	200-EHT10501LDSMPTR
EHT-108-01-S-D	200-EHT10801SD	EHT-108-01-L-D	200-EHT10801LD
EHT-108-01-S-D-RA	200-EHT10801SDRA	EHT-108-01-L-D-RA	200-EHT10801LDRA
EHT-108-01-S-D-SM	200-EHT10801SDSM	EHT-108-01-L-D-SM	200-EHT10801LDSM
EHT-108-01-S-D-SM-K-TR	200-EHT10801SDSMKTR	EHT-108-01-L-D-SM-K-TR	200-EHT10801LDSMKTR
EHT-108-01-S-D-SM-LC	200-EHT10801SDSMLC	EHT-108-01-L-D-SM-LC	200-EHT10801LDSMLC
EHT-108-01-S-D-SM-P-TR	200-EHT10801SDSMPTR	EHT-108-01-L-D-SM-P-TR	200-EHT10801LDSMPTR
EHT-108-01-S-D-SM-TR	200-EHT10801SDSMTR	EHT-108-01-L-D-SM-TR	200-EHT10801LDSMTR
EHT-110-01-H-D	200-EHT-110-01-H-D	EHT-110-01-L-D	200-EHT11001LD
EHT-110-01-H-D-SM-P-TR	200-EHT-11001HDSMPTR	EHT-110-01-L-D-SM-P-TR	200-EHT11001LDSMPTR
EHT-110-01-S-D	200-EHT11001SD	EHT-110-01-L-D	200-EHT11001LD
EHT-110-01-S-D-RA	200-EHT11001SDRA	EHT-110-01-L-D-RA	200-EHT11001LDRA
EHT-110-01-S-D-SM	200-EHT11001SDSM	EHT-110-01-L-D-SM	200-EHT11001LDSM
EHT-110-01-S-D-SM-K-TR	200-EHT11001SDSMKTR	EHT-110-01-L-D-SM-K-TR	200-EHT11001LDSMKTR
EHT-110-01-S-D-SM-LC	200-EHT11001SDSMLC	EHT-110-01-L-D-SM-LC	200-EHT11001LDSMLC
EHT-110-01-S-D-SM-P-TR	200-EHT11001SDSMPTR	EHT-110-01-L-D-SM-P-TR	200-EHT11001LDSMPTR
EHT-112-01-S-D	200-EHT11201SD	EHT-112-01-L-D	200-EHT11201LD
EHT-112-01-S-D-RA	200-EHT11201SDRA	EHT-112-01-L-D-RA	200-EHT11201LDRA
EHT-112-01-S-D-SM-P-TR	200-EHT11201SDSMPTR	EHT-112-01-L-D-SM-P-TR	200-EHT11201LDSMPTR
EHT-113-01-H-D	200-EHT-113-01-H-D	EHT-113-01-L-D	200-EHT11301LD
EHT-113-01-S-D	200-EHT11301SD	EHT-113-01-L-D	200-EHT11301LD

Gold Option	Gold Mouser Part Number	Cost-Optimized Alternative	Cost-Optimized Alternative Mouser Part Number
EHT-113-01-S-D-SM-TR	200-EHT11301SDSMTR	EHT-113-01-L-D-SM-TR	200-EHT11301LDSMTR
EHT-115-01-H-D-SM-P-TR	200-EHT-11501HDSMPTR	EHT-115-01-L-D-SM-P-TR	200-EHT11501LDSMPTR
EHT-115-01-S-D	200-EHT11501SD	EHT-115-01-L-D	200-EHT11501LD
EHT-115-01-S-D-SM-K-TR	200-EHT11501SDSMKTR	EHT-115-01-L-D-SM-K-TR	200-EHT11501LDSMKTR
EHT-115-01-S-D-SM-LC	200-EHT11501SDSMLC	EHT-115-01-L-D-SM-LC	200-EHT11501LDSMLC
EHT-115-01-S-D-SM-P-TR	200-EHT11501SDSMPTR	EHT-115-01-L-D-SM-P-TR	200-EHT11501LDSMPTR
EHT-117-01-H-D	200-EHT-117-01-H-D	EHT-117-01-L-D	200-EHT11701LD
EHT-117-01-S-D	200-EHT11701SD	EHT-117-01-L-D	200-EHT11701LD
EHT-117-01-S-D-RA	200-EHT11701SDRA	EHT-117-01-L-D-RA	200-EHT11701LDRA
EHT-117-01-S-D-SM	200-EHT11701SDSM	EHT-117-01-L-D-SM	200-EHT11701LDSM
EHT-120-01-H-D	200-EHT-120-01-H-D	EHT-120-01-L-D	200-EHT12001LD
EHT-120-01-S-D	200-EHT12001SD	EHT-120-01-L-D	200-EHT12001LD
EHT-120-01-S-D-RA	200-EHT12001SDRA	EHT-120-01-L-D-RA	200-EHT12001LDRA
EHT-120-01-S-D-SM	200-EHT12001SDSM	EHT-120-01-L-D-SM	200-EHT12001LDSM
EHT-120-01-S-D-SM-LC	200-EHT12001SDSMLC	EHT-120-01-L-D-SM-LC	200-EHT12001LDSMLC
EHT-122-01-S-D-SM-P-TR	200-EHT12201SDSMPTR	EHT-122-01-L-D-SM-P-TR	200-EHT-12201LDSMPTR
EHT-125-01-H-D	200-EHT-125-01-H-D	EHT-125-01-L-D	200-EHT12501LD
EHT-125-01-H-D-SM-P-TR	200-EHT-12501HDSMPTR	EHT-125-01-L-D-SM-P-TR	200-EHT12501LDSMPTR
EHT-125-01-S-D	200-EHT12501SD	EHT-125-01-L-D	200-EHT12501LD
EHT-125-01-S-D-SM-K-TR	200-EHT12501SDSMKTR	EHT-125-01-L-D-SM-K-TR	200-EHT12501LDSMKTR
EHT-125-01-S-D-SM-LC	200-EHT12501SDSMLC	EHT-125-01-L-D-SM-LC	200-EHT12501LDSMLC
EHT-125-01-S-D-SM-LC-K	200-EHT12501SDSMLCK	EHT-125-01-L-D-SM-LC-K	200-EHT12501LDSMLCK
EHT-125-01-S-D-SM-P-TR	200-EHT12501SDSMPTR	EHT-125-01-L-D-SM-P-TR	200-EHT12501LDSMPTR