

FFC, FPC Cable Connectors ***HF601 Series***

HF601 FFC/FPC Connectors

- ZIF Style Connector Design
- Transmission speed: 1 ~ 3Gbps
(HF601-22-03 only)
- Pitch: 0.50 mm
- Available Pin Count: 10 – 60pins



Product PN	Available Pin Count	Description	Design Option
HF601-XX-02	10, 20, 26, 30, 40, 45, 50, 60	Receptacle Connectors	Right Angle Mount
HF601-XX-12	20, 30, 40, 45, 50	Receptacle Connectors	Vertical Mount
HF601-22-03	22	Receptacle Connectors	Right Angle Mount

CAU002 HF601 Support Cable

- FFC/FPC Cable Designs
- Offering various pin count options
(20 ~ 50pin)
- Pitch: 0.50 mm
- Available Length: 100, 600, 900mm L



Product PN	Available Pin Count	Description	Design Option
CAU002-XXX-050-XXXX	20, 30, 40, 50	HF601 Series Support FFC/FPC Cable	0.5mm Pitch, 100/600/900mm L