

## INTRODUCING

# NECTOR T PLUGGABLE CONNECTORS

- Easy to install and repair with standard tools
- Provides flexibility and material cost savings during installation by reducing waste



TE Connectivity (TE)'s NECTOR T Pluggable connectors provide an easy-to-use, pluggable power-distribution connector-cabling system, suited for moist and wet environments (sealed IP68). NECTOR T pluggable connectors offer a complete solution including 3-way and 4-way splitters and panel mount connectors, so power-splitting is fast and easy. Installation is quick and flexible with both crimp and screw type terminals.

These sealed pluggable connectors are used specifically and offer a new solution to high humidity and harsh environment applications like garden lighting, horticultural lighting, building facade lighting and other outdoor installations.

### KEY BENEFITS

- Allows pre-terminated cables with lower labor/installation costs
- Protects against UV (sun light) rain and dust for use outdoors without functional failure due to the environment providing long-life and reliability
- Provides protection to the mating interface in an unmated/open condition
- Eliminates mis-mating and potential re-work

### APPLICATIONS

- Horticultural lighting installations
- Farm lights
- Grow light connections
- Sealed power distribution

### MECHANICAL

- Cable gland range:
  - Range 1: Ø7 to Ø11 mm
  - Range 2: Ø11 to Ø15 mm
- Polarizing key A & B
- Crimp terminal range:
  - 1.5 mm<sup>2</sup> or 16 AWG
  - 2.5 mm<sup>2</sup> or 14 AWG
  - 4.0 mm<sup>2</sup> or 12 AWG
- IP rated: IP67, IP68

### ELECTRICAL

- 600 Vac (UL)
- 500 Vac (IEC)
- 10 to 25 Amp

### STANDARD

- UL 2238
- IEC 61535-1

### MATERIALS

- PBT + PC resin with UL 94 VO & UV F1 rating
- Contacts high performance copper alloy

### SPECIFICATIONS

- Application Spec: [114-133123](#)
- Product Spec: [108-133123](#)

### LEARN MORE

[NECTOR T Pluggable Product Page](#)  
[NECTOR T Pluggable Product Flyer](#)  
[NECTOR T Pluggable Part Number List](#)