

Fir Tree Mount Cable Ties

2-Piece Fir Tree Mount and Cable Tie Assemblies

PART NO.	TYPE	Min. Tensile Strength lbs. (N)	Max. Bundle Diameter in. (mm)	Length (L) in. (mm)	Mounting Hole Dia. in. (mm)	Panel Thickness in. (mm)	Material Cable Tie	Material Fir Tree	Color	Pkg. Qty.
156-00882	T50RFT 5.5SD	50.0 (225.0)	2.0 (45.0)	8.0 (203.2)	0.2 - 0.22 (5.0 - 5.7)	0.03-0.12 (0.7-4.5)	PA66HS	PA66HIRHS	Black	500
156-00457	T50RFT7HD	50.0 (225.0)	1.8 (50.0)	8.0 (200.0)	0.24 - 0.28 (6.2 - 7.2)	0.03-0.28 (0.8-7.0)	PA46	PA46	Brown	500
156-00329		50.0 (225.0)	1.8 (45.0)	8.0 (200.0)	0.24 - 0.28 (6.3 - 7.1)	0.03-0.28 (0.8-7.0)	PA66HS	PA66HIRHS	Black	500
150-31093	T50SFT6LG	50.0 (225.0)	1.4 (30.0)	6.0 (160.0)	0.25 - 0.28 (6.5 - 7.0)	0.03-0.24 (0.75-6.0)	PA66HS	PA66HIRHS	Black	500
150-31098	T50RFT6LG	50.0 (222.0)	2.0 (45.0)	8.0 (200.0)	0.25 - 0.28 (6.5 - 7.0)	0.03-0.24 (0.75-6.0)	PA46	PA46	Gray	500
150-31091		50.0 (225.0)	2.0 (45.0)	8.0 (202.0)	0.25 - 0.28 (6.5 - 7.0)	0.03-0.24 (0.75-6.0)	PA66HS	PA66HIRHS	Black	500
156-00157	T50RFT6	50.0 (225.0)	2.0 (45.0)	8.0 (202.0)	0.25 - 0.28 (6.4 - 7.1)	0.03-0.12 (0.75-3.0)	PA66HS	PA66HIRHS	Black	500
156-00156	T50SFT6	50.0 (225.0)	1.4 (35.0)	6.0 (160.0)	0.26 - 0.28 (6.5 - 7.0)	0.03-0.12 (0.75-3.0)	PA66HS	PA66HIRHS	Black	500
156-00056	T50SFT7	50.0 (225.0)	1.4 (35.0)	6.0 (160.0)	0.26 - 0.28 (6.5 - 7.0)	0.03-0.28 (0.8-7.0)	PA66HS	PA66HS	Black	500
111-85871	T50RFT7	50.0 (225.0)	2.0 (45.0)	7.9 (202.0)	0.26 - 0.28 (6.5 - 7.0)	0.03-0.28 (0.8-7.0)	PA66HS	PA66HS	Black	500
111-05350	T50IFT7	50.0 (225.0)	3.3 (85.0)	11.8 (305.0)	0.26 - 0.28 (6.5 - 7.0)	0.03-0.28 (0.8-7.0)	PA66HS	PA66HS	Black	500
156-00054	T50IFT6LG	50.0 (225.0)	3.3 (85.0)	12.0 (305.0)	0.26 - 0.28 (6.5 - 7.0)	0.03-0.24 (0.75-6.0)	PA66HS	PA66HIR	Black	500
156-00066	T50LFT6	50.0 (225.0)	4.3 (110.0)	15.0 (390.0)	0.26 - 0.28 (6.5 - 7.0)	0.03-0.12 (0.75-3.0)	PA66HS	PA66HIRHS	Black	500
156-00055	T50LFT7	50.0 (225.0)	4.3 (110.0)	15.0 (390.0)	0.26 - 0.28 (6.5 - 7.0)	0.03-0.28 (0.8-7.0)	PA66HS	PA66HS	Black	500
156-00282		50.0 (225.0)	3.4 (85.0)	15.0 (380.0)	0.26 - 0.28 (6.5 - 7.0)	0.03-0.28 (0.8-7.0)	PA66HS	PA66HS	Black	500
156-00376	T50RFT8	50.0 (225.0)	1.8 (48.0)	8.0 (202.0)	0.3 - 0.31 (7.7 - 8.0)	0.02-0.26 (0.8-6.0)	PA66HS	PA66HS	Black	500
156-00377	T50IFT8	50.0 (225.0)	3.4 (81.0)	12.0 (305.0)	0.3 - 0.31 (7.7 - 8.0)	0.03-0.24 (0.8-5.0)	PA66HS	PA66HS	Black	500
156-00378	T50LFT8	50.0 (225.0)	4.2 (105.0)	15.0 (380.0)	0.3 - 0.31 (7.7 - 8.0)	0.03-0.20 (0.8-5.0)	PA66HS	PA66HS	Black	500

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.
Installation tools: EVO7, EVO7SP, EVO9, EVO9HT, MK7P, MK7HT, MK9P.

Bundling and Securing

Self-Affixing Cable Ties

Fir Tree Mount Cable Ties

2-Piece Fir Tree Mount and Cable Tie Assemblies

PART NO.	TYPE	Min. Tensile Strength lbs. (N)	Max. Bundle Diameter in. (mm)	Length (L) in. (mm)	Mounting Hole Dia. in. (mm)	Panel Thickness in. (mm)	Material Cable Tie	Material Fir Tree	Color	Pkg. Qty.
156-00091	T50RFT10	50.0 (225.0)	1.8 (45.0)	8.0 (203.2)	0.38 - 0.39 (9.7 - 10.0)	0.03-0.20 (0.8-5.0)	PA66HS	PA66HS	Black	500
111-85810		50.0 (225.0)	1.8 (45.0)	8.0 (200.0)	0.38 - 0.39 (9.7 - 10.0)	0.03-0.20 (0.8-5.0)	PA66HS	PA66HS	Black	500
156-00092	T50IFT10	50.0 (225.0)	3.4 (81.0)	12.0 (305.0)	0.38 - 0.39 (9.7 - 10.0)	0.03-0.20 (0.8-5.0)	PA66HS	PA66HS	Black	500
156-00093	T50LFT10	50.0 (225.0)	4.3 (110.0)	15.0 (380.0)	0.38 - 0.39 (9.7 - 10.0)	0.03-0.20 (0.8-5.0)	PA66HS	PA66HS	Black	500
156-01336	PT2AFT6LG	51.7 (230.0)	1.4 (35.0)	5.7 (145.0)	0.25 - 0.28 (6.4 - 7.1)	0.03-0.24 (0.75-6.0)	PEEK	PA46	Beige, Gray	500
156-01555	PAT100R FT6LG	100.0 (445.0)	1.4 (35.0)	5.9 (149.9)	0.22 - 0.25 (5.6 - 6.4)	0.05-0.24 (1.25-6.0)	PAEK	PAEK	Beige	500
156-01513	PAT100L FT6LG	100.0 (445.0)	2.0 (50.8)	7.9 (200.7)	0.22 - 0.25 (5.6 - 6.4)	0.05-0.24 (1.25-6.0)	PAEK	PAEK	Beige	500
156-00068	WSSFT9A	120.0 (535.0)	2.3 (57.0)	9.0 (228.0)	0.34 - 0.36 (8.7 - 9.2)	0.04-0.26 (1.0-6.5)	PA66HIRHSUV	PA66HIRHSUV	Black	100
156-00072	WSSFT9B	120.0 (535.0)	2.3 (57.0)	9.0 (228.0)	0.34 - 0.36 (8.7 - 9.2)	0.04-0.62 (1.0-15.8)	PA66HS	PA66HIRHSUV	Black	100
156-00071	T120RFT9B	120.0 (535.0)	4.0 (100.0)	15.0 (380.0)	0.34 - 0.36 (8.7 - 9.2)	0.04-0.62 (1.0-15.8)	PA66HS	PA66HIRHSUV	Black	100
156-00067	T120RFT9A	120.0 (535.0)	4.0 (100.0)	15.0 (380.0)	0.34 - 0.36 (8.7 - 9.2)	0.04-0.26 (1.0-6.5)	PA66HS	PA66HIRHSUV	Black	100
156-00069	WSIFT9A	120.0 (535.0)	4.0 (102.0)	15.0 (387.0)	0.34 - 0.36 (8.7 - 9.2)	0.04-0.62 (1.0-6.5)	PA66HS	PA66HIRHSUV	Black	100
156-00070	WSRFT9A	120.0 (535.0)	4.1 (105.0)	15.0 (380.0)	0.34 - 0.36 (8.7 - 9.2)	0.04-0.62 (1.0-6.5)	PA66HS	PA66HIRHSUV	Black	100
156-00074	WSRFT9B	120.0 (535.0)	4.1 (105.0)	15.0 (380.0)	0.34 - 0.36 (8.7 - 9.2)	0.04-0.62 (1.0-15.8)	PA66HS	PA66HIRHSUV	Black	100

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.
Installation tools: EVO7, EVO7SP, EVO9, EVO9HT, MK7P, MK7HT, MK9P.