

Low-Profile Vertical Wall-Mount Rack (135 lb) *VPB Series*

Space-saving rack solution designed to support deep equipment in shallow installations without a full cabinet.

TOP SELLER



Key Features and Benefits

- Vertical mounting design (19" rack compatible) supports deep equipment in shallow spaces where free-standing cabinets will not fit.
- 14-gauge steel construction (135 lb **capacity**) provides reliable support for switches, patch panels, and network equipment.
- Open access with rear cable routing enables faster installation, improved airflow, and simplified cable management.
- Compact, cost-effective alternative to cabinets reduces footprint and overall project cost.
- TAA-compliant, RoHS compliant, manufactured in North America ensures regulatory compliance, quality, and supply reliability.
- Black powder coat finish (GREENGUARD Gold, TSCA, and RoHS compliant) provides a low-emitting, corrosion-resistant finish suitable for indoor environments.

The VPB Series vertical wall-mount rack is a space-saving solution for mounting 19-inch rack equipment in environments where traditional cabinets or racks will not fit. By orienting equipment vertically, it supports deeper devices in shallow spaces while maintaining accessibility and structural strength.

Commonly used in telecom rooms, small network closets, and retrofit installations, the VPB is ideal where floor space is unavailable but reliable equipment support is required. Compared to enclosed cabinets, it offers a compact, cost-effective option for installations that prioritize space efficiency and open access.

When Another Product May Be a Better Choice

- When you need a minimal, low-cost solution for light equipment, consider our **RB-CW** Series.
- When you need security or enclosure, consider our wall-mount cabinet solutions.
- When you need environmental protection (dust or water), consider our **NWC** or **NWM** Series cabinets.

Gallery



Accessories

- Universal Rack Shelf Fixed Steel (Up to 200 lb Capacity)
- Hinged Window Rack Security Cover

- Mounting Screw and Clip Nut Combo-Pack
- Ground Stud Kit
- We Manufacture PDUs and Outlet Strips

Part No.	Overall Dimensions			Rack Units	Mounting Dimensions	
	Height	Width	Depth		Height	Width
VPB192UBK	7.69	19.19	4.19	2U	3.50	19.00
VPB194UBK	7.69	19.19	7.69	4U	7.00	19.00
VPB196UBK	11.19	19.19	11.19	6U	10.50	19.00

6U Ships unassembled in a flat-pack.

What's Inside the Box

Qty Included	Description	Replacement Part No.
1	Wall Bracket	
10	10-32 x 0.75in Rack Mounting Screws	SCREW1032-10

Where the VPB Series Works Best

- Tight network closets with limited depth.
- Telecom backboards and communication rooms.
- Retail and branch locations.
- Office IT spaces without floor space.
- Retrofit and space-constrained installations.

Applications and when to use the VPB Series

- You need to mount deep equipment in a shallow space.
- Floor space is limited or unavailable.
- You want a low-profile alternative to a full cabinet.
- Quick installation and open access are priorities.

Tags: **Vertical Rack Bracket, Vertical Low Profile, Vertical Rack, Hub-brackets, knock-down, knock down, vp8194ubk, vp8** *Data subject to change without notice.*