

Specification Sheet

Part Number: 151-04157



Temporarily holds wires along routing path until ready to make permanent.

Built-in CutZone safety feature prevents damage to wires and cables.

Unique EZ Feed slot maintains clear space to insert cable ties.

Allows flexibility of frame size and mounting location with #8 (M4) screw into panel surface or with T-nut in frame.

Cradle Mount With Screw Attachment, 0.24" Cradle Area, 4.5mm Screw Hole Dia, PA66STHS, Black, 100/Pkg

Article Number 151-04157

Type CTCM6CZS

Color Black (BK)

Quantity Per bag

Product Description

The cradle mount with screw attachment fastens with a screw and T-nut and is ideal for routing wires in industrial applications where rework and adjustments are common. Mount features a 0.24" cradle opening for cable retention. The cradle arms can temporarily hold wires for simple adjustments and cable additions and protect against abrasion and cable damage. To permanently mount the bundle, the EZ Feed cable tie slot eliminates common obstructions for faster completion. During rework, the CutZone prevents wire damage when cutting off cable ties.

Short Description	Cradle Mount With Screw Attachment, 0.24" Cradle Area, 4.5mm Screw Hole Dia, PA66STHS, Black, 100/Pkg
Global Part Name	CTCM6CZS-PA66STHS-BK
Length L (Imperial)	1.0
Length L (Metric)	25.4
Fixation Method	Screw Mounting and T-Nut
Width W (Imperial)	0.76
Width W (Metric)	19.3
Height H (Imperial)	0.55
Height H (Metric)	14.0
Cable Tie Width Max (Imperial)	0.36
Cable Tie Width Max (Metric)	9.07
Mounting Hole Diameter D (Imperial)	0.18
Mounting Hole Diameter D (Metric)	4.5 mm
Material	Polyamide 6.6, super tough, heat stabilized (PA66STHS)

Material Shortcut

PA66STHS

Flammability

UL 94 HB

Halogen Free

Yes

UV Resistant (Yes/No)

No

Operating Temperature

-40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33)

Yes

ROHS Compliant

Yes

Package Quantity (Imperial)

100

Package Quantity (Metric)

100

Customs Number

3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)