

Bundling and Securing

Mounts


Proximity Sensor Mounts

For Cylindrical/Tubular-Style Sensors


The sensor mount product family is a system of mounting, positioning and wire management devices designed for proximity sensors used on conveyors and industrial automation equipment. The unique retention slot feature quickly positions and retains the sensor locknut, which simplifies installation and repositioning. Hybrid construction with galvanized steel mounting plate reduces weight, tolerates high torque and adds stability. Attach with an M6 or #10 mounting screw.

Features and Benefits

- Vertical slotted pocket design allows easier assembly and adjustability.
- Integrated retaining gap allows for single-tool tightening.
- Locating grooves create a visual reference point for easier sensor alignment.
- Multiple mounting slot positions for quick assembly and cable tie mount to manage excess cable loops.



MATERIAL	Polyphenylene Sulfide (PPS), Steel (ST), Zinc plated (ZN)
Color	Black (BK)



PART NO.	TYPE	Fits Sensor Size	Length (L) in. (mm)	Width (W) in. (mm)	Height (H) in. (mm)	Mounting Hole Dia. in. (mm)	Mounting Screw Type	Color	Pkg. Qty.
151-04215	SENMT18M6	18 mm	1.8 (46.7)	1.5 (38.0)	1.9 (47.5)	0.2 (4.3)	#10.0 (M6) Screw	Black	100

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.

HellermannTyton

HellermannTyton North American Corporate Headquarters

7930 N. Faulkner Rd, PO Box 245017
Milwaukee, WI 53224-9517
Phone: (414) 355-1130, (800) 537-1512
Fax: (414) 355-7341, (800) 848-9866
email: corp@htamericas.com
www.hellermann.tyton.com

IATF 16949, AS9100, ISO 9001 and ISO14001 certified

HellermannTyton Canada

Unit #4, 205 Industrial Parkway North
Aurora, Ontario L4G 4C4 Canada
Phone: (800) 661-2461
Fax: (800) 390-3904
email: sales@hellermanntyton.ca

HellermannTyton Mexico

Anillo Periferico Sur 7980 Edificio 6A
Parque Industrial Tecnológico II
Santa María Tequexpan
Tlaquepaque, Jalisco, Mexico 45601
Phone: 011-52-33-3-133-9880
Fax: 011-52-33-3-133-9861
email: info-mx@hellermanntyton.com

ISO 9001 certified

Warranty Policy – HellermannTyton products are warranted to be free from defects in material and workmanship at the time sold by us; but our obligation under this warranty and that of the seller is limited to the replacement of the product, and neither we nor the seller are bound by any other warranty, expressed, implied or statutory. Under no circumstances are we or the seller liable for any loss, damage, expenses or consequential damages of any kind arising out of the use or inability to use these products. All are sold with the understanding that the user will test them in actual use and determine their adaptability for the intended uses.