


THROUGH-HOLE .025" SQ POST HEADER

(2.54 mm) .100" PITCH • TSW/HTSW SERIES



TSW/HTSW

Board Mates:

SSW, SSQ, SSM, ESW, ESQ,
BCS, BSW, CES, SLW

Cable Mates:

IDSD, IDSS

SPECIFICATIONS

Insulator Material:

TSW: PBT

HTSW: Natural LCP

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over 50 μ" (1.27 μm) Ni

Operating Temp Range:

-55 °C to +125 °C with Gold

-55 °C to +105 °C with Tin

Voltage Rating:

550 VAC mated with SSW;

500 VAC mated with BCS;

515 VAC mated with ESQ;

450 VAC -RA/-RE mated

with BCS or SSM;

400 VAC mated with CES

Lead-Free Solderable:

HTSW: Yes

TSW: No, Lead Wave Only

CURRENT RATING (PER PIN)

TSW mated with

| ESW | SSW | SLW | SSQ | SSM | BCS | SNT |
|-------|-------|-------|-------|-------|-------|-------|
| 5.2 A | 5.7 A | 5.2 A | 6.3 A | 5.2 A | 4.6 A | 4.3 A |

2 POSITIONS POWERED

ALSO AVAILABLE MOQ Required

Other Platings

OTHER SOLUTIONS

Elevated Right-angle option
Shunts

Note:

Some lengths, styles and
options are non-standard,
non-returnable.

SERIES

TSW

= Standard Strip

HTSW

= Hi-Temp Strip

PIN CENTERS

-1

= .100" (2.54 mm) Centers,
(All positions filled)

-2

= .200" (5.08 mm) Centers,
(Every other position filled)

NO. PINS PER ROW

01 thru 50



= .100" (2.54 mm)
Center Version

02 thru 25

= .200" (5.08 mm)
Center Version

LEAD STYLE

Specify
LEAD STYLE
from chart



Straight Pin Versions

STRAIGHT PIN VERSIONS

| LEAD STYLE | A | B | C |
|------------|---------------|--------------|-------------|
| *-05 | (8.51) .335 | (3.30) .130 | (2.67) .105 |
| *-06 | (7.62) .300 | (2.41) .095 | (2.67) .105 |
| *-07 | (10.92) .430 | (2.54) .100 | |
| *-08 | (13.46) .530 | (5.08) .200 | |
| -09 | (18.54) .730 | (10.16) .400 | |
| -10 | (21.08) .830 | (12.70) .500 | (5.84) .230 |
| -11 | (23.62) .930 | (15.24) .600 | |
| -12 | (26.16) 1.030 | (17.78) .700 | |
| -13 | (31.24) 1.230 | (22.86) .900 | |
| -14 | (13.46) .530 | (2.79) .110 | (8.13) .320 |
| *-15 | (18.54) .730 | (13.21) .520 | |
| *-16 | | (7.87) .310 | (8.13) .320 |
| *-17 | (21.08) .830 | (15.74) .620 | |
| *-18 | (23.62) .930 | (18.29) .720 | |

* Available with -LL (Locking Lead) Option


Specify -07 for best mate with IDXX Series IDC Cable

STRAIGHT PIN VERSIONS

| LEAD STYLE | A | B | C |
|------------|---------------|---------------|---------------|
| *-19 | (26.16) 1.030 | (2.79) .110 | (20.83) .820 |
| *-20 | (31.24) 1.230 | | (25.91) 1.020 |
| *-21 | (36.32) 1.430 | (2.79) .110 | (30.99) 1.220 |
| *-22 | (16.00) .630 | (7.62) .300 | (5.84) .230 |
| *-23 | (11.30) .445 | (2.92) .115 | (6.73) .265 |
| *-24 | (12.15) .480 | | (8.13) .320 |
| *-25 | (16.00) .630 | (5.33) .210 | |
| ▲-26 | (11.58) .456 | (3.20) .126 | |
| -27 | (33.78) 1.330 | (25.40) 1.000 | (5.84) .230 |
| -28 | (28.70) 1.130 | (20.32) .800 | |
| -29 | (33.78) 1.330 | (23.11) .910 | (8.13) .320 |
| -30 | (28.70) 1.130 | (18.03) .710 | |
| +41 | (9.27) .365 | (0.89) .035 | (5.84) .230 |
| +42 | (11.94) .470 | (1.27) .050 | (8.13) .320 |

† Style -41 & -42 available with HTSW only.

▲ Except: Style -26 (0.46) .018 DIA Tail







PLATING OPTION

-F
= Gold flash on post, Matte Tin on tail

-GF
= 3 μ " (0.07 μ m) Gold on post and tail

-L
= 10 μ " (0.25 μ m) Gold on post, Matte Tin on tail

-T
= Matte Tin



Right-Angle Versions

| LEAD STYLE | D |
|------------|-------------|
| -RA | (1.52) .060 |
| -RE | (4.06) .160 |

| RIGHT-ANGLE VERSIONS | | |
|----------------------|-------------|--------------|
| -RE LEAD STYLE | C | SINGLE E |
| -09 | (5.84) .230 | (4.83) .190 |
| -10 | | (7.37) .290 |
| -11 | | (9.91) .390 |
| -12 | | (12.45) .490 |
| -13 | | (17.53) .690 |
| -16 | (8.13) .320 | (2.54) .100 |
| -21 | (5.84) .230 | (22.61) .890 |
| -22 | | (2.29) .090 |
| -27 | | (20.07) .790 |
| -28 | | (14.99) .590 |
| -28 | | (14.99) .590 |





ROW OPTION

-S
= Single Row

-D
= Double Row

-T
= Triple Row

-Q
= Double Row
(5.08 mm) .200" row space



OTHER OPTION

-RA or -RE
= Right-angle

-NA
= Right-angle
(Using straight body for coplanar mating with SSW-RA series)

-LL
= Locking Lead
See charts for available styles.
Not available with single row
1 or 2 positions.
Recommended hole size
(1.02 mm \pm 0.03 mm) .040" \pm .001

-LC
= Locking Clip
(Styles -08 thru -13 & -22 only)
(Requires 4 pin minimum)
(Not available with T, -Q, -RA or -RE)

-LA
= -RA Option with -LL Option

-"XXX"
= Polarized Position

| -RA LEAD STYLE | RIGHT-ANGLE VERSIONS | | | |
|----------------|----------------------|--------------|--------------|------------------|
| | SINGLE (-S) | | DOUBLE (-D) | TRIPLE (-T & -Q) |
| | C | E | E | E |
| -08 | (5.84) .230 | (2.29) .090 | (2.29) .090 | (2.29) .090 |
| -09 | | (7.37) .290 | (7.37) .290 | (7.37) .290 |
| -10 | | (9.91) .390 | (9.91) .390 | (9.91) .390 |
| -11 | | (12.45) .490 | (12.45) .490 | (12.45) .490 |
| -12 | | (14.99) .590 | (14.99) .590 | (14.99) .590 |
| -13 | | (20.07) .790 | (20.07) .790 | N/A |
| *-16 | (8.13) .320 | (5.08) .200 | (5.08) .200 | (5.08) .200 |
| -21 | (5.84) .230 | (25.15) .990 | N/A | N/A |
| *-22 | | (4.83) .190 | (4.83) .190 | (4.83) .190 |
| *-25 | (8.13) .320 | (2.54) .100 | (2.54) .100 | (2.54) .100 |
| -27 | (5.84) .230 | (22.61) .890 | N/A | N/A |
| -28 | | (17.53) .690 | (17.53) .690 | |
| -29 | (8.13) .320 | (20.32) .800 | N/A | |
| -30 | | (15.24) .600 | (15.24) .600 | |

* Available with -LA (Locking Lead) Option

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[HTSW-103-07-G-D](#) [HTSW-102-07-T-S](#) [HTSW-106-07-G-S](#) [HTSW-102-07-G-S](#) [HTSW-130-05-S-D](#) [HTSW-139-05-S-D](#) [HTSW-121-25-S-S-RA](#) [HTSW-103-08-S-S-LL](#) [HTSW-110-25-S-D-RA](#) [HTSW-113-23-L-D](#) [HTSW-102-07-L-S](#) [HTSW-108-08-S-D-LL](#) [HTSW-102-14-L-D](#) [HTSW-104-14-L-D](#) [HTSW-105-05-T-T](#) [HTSW-104-08-T-D-RA](#) [HTSW-113-08-S-D-RA](#) [HTSW-128-07-T-S](#) [HTSW-135-05-S-T](#) [HTSW-136-07-TM-S](#) [HTSW-101-26-L-T](#) [HTSW-101-08-S-S](#) [HTSW-102-05-G-S](#) [HTSW-102-05-T-S](#) [HTSW-102-23-SM-S](#) [HTSW-101-07-S-D](#) [HTSW-102-17-T-S](#) [HTSW-103-18-S-S-LL](#) [HTSW-102-26-S-S](#) [HTSW-105-06-G-S](#) [HTSW-103-14-T-S](#) [HTSW-102-08-L-D-RA](#) [HTSW-105-06-TM-S](#) [HTSW-104-07-L-D-002](#) [HTSW-105-23-T-T](#) [HTSW-103-07-L-D](#) [HTSW-105-15-LM-D](#) [HTSW-105-09-S-D-RA](#) [HTSW-107-08-G-D-006](#) [HTSW-107-08-T-D](#) [HTSW-108-24-S-S](#) [HTSW-110-08-L-D-LA](#) [HTSW-105-07-T-S](#) [HTSW-108-23-T-S](#) [HTSW-113-08-T-S-RA](#) [HTSW-108-07-G-D-LL](#) [HTSW-110-23-S-S](#) [HTSW-110-24-L-D](#) [HTSW-116-14-L-D](#) [HTSW-120-08-G-D-LC](#) [HTSW-107-07-L-D](#) [HTSW-117-07-L-D](#) [HTSW-110-14-L-D](#) [HTSW-108-07-S-S](#) [HTSW-108-13-L-S](#) [HTSW-109-07-G-S](#) [HTSW-110-08-L-D-RA](#) [HTSW-122-07-L-D](#) [HTSW-116-07-L-D](#) [HTSW-118-16-T-S](#) [HTSW-150-26-G-D](#) [HTSW-118-22-T-S-RA](#) [HTSW-203-07-S-S](#) [HTSW-118-09-T-D-RA](#) [HTSW-204-14-L-S](#) [HTSW-150-14-G-S](#) [HTSW-128-22-T-S-RA](#) [HTSW-150-14-L-D](#) [HTSW-101-14-L-S](#) [HTSW-102-08-F-D-RA](#) [HTSW-102-06-T-S](#) [HTSW-101-05-L-D](#) [HTSW-103-07-LM-S](#) [HTSW-102-14-G-S](#) [HTSW-103-07-L-S-LL](#) [HTSW-102-24-T-S](#) [HTSW-103-15-T-D](#) [HTSW-104-07-L-S](#) [HTSW-103-23-T-S](#) [HTSW-101-08-T-D-RA](#) [HTSW-103-24-G-S](#) [HTSW-102-22-S-D-RA](#) [HTSW-104-13-G-D](#) [HTSW-105-08-T-S-RA](#) [HTSW-102-23-L-D](#) [HTSW-103-05-G-S](#) [HTSW-104-09-G-S-RE](#) [HTSW-105-14-T-S](#) [HTSW-103-14-G-D-004](#) [HTSW-104-08-F-D-RA](#) [HTSW-102-10-T-S-RE](#) [HTSW-103-08-T-S-RA](#) [HTSW-103-14-T-D](#) [HTSW-104-08-T-S-RA](#) [HTSW-105-16-G-D](#) [HTSW-106-09-G-S-RA](#) [HTSW-106-07-L-D](#) [HTSW-106-25-L-S-RA](#) [HTSW-104-26-G-D](#) [HTSW-107-23-S-D](#)