



Product: [7922A](#) 

DataTuff® Cat 5e, 4 Bonded-Pr #22 Sol BC, PO Ins, PVC Jkt, PLTC CMR/CMX-Outdoor

 [Request Sample](#)

Product Description

Industrial Ethernet Cat 5e, 4 Bonded-Pair 22AWG (Solid) Bare Copper, PO Insulation, PVC Outer Jacket, PLTC CMR/CMX-Outdoor

Technical Specifications

Product Overview

Suitable Applications:	power-limited tray, harsh environment, IIoT, factory or process automation, IP cameras and devices, data communication, etc.
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/patents .

Construction Details

Conductor

Element	Size	Stranding	Material	No. of Pairs
Pair(s)	22 AWG	Solid	BC - Bare Copper	4

Insulation

Material	Color Code
PO - Polyolefin	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown

Bonded-Pair:	Yes
--------------	-----

Outer Jacket

Material	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.301 in (7.65 mm)	Yes

Overall Cable Diameter (Nominal):	0.301 in (7.65 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Capacitance Unbalance
56.5 Ohm/km (17.2 Ohm/1000ft)	66 pF/100m

Delay

Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.
510 ns/100m	25 ns/100m	70%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted) [Ohm]	Max./Min. Fitted Impedance [Ohm]
1	2.0 dB/100m	65.3	65.3	63.3	63.3	63.8	60.8	20	100 ± 12	105 ± 10
4	4.0 dB/100m	56.3	56.3	52.3	52.3	51.7	48.7	23	100 ± 12	100 ± 10
8	5.7 dB/100m	51.8	51.8	46.1	46.1	45.7	42.7	24.5	100 ± 12	100 ± 10
10	6.4 dB/100m	50.3	50.3	43.9	43.9	43.8	40.8	25	100 ± 12	100 ± 10
16	8.1 dB/100m	47.3	47.3	39.1	39.1	39.7	36.7	25	100 ± 12	100 ± 10
20	9.2 dB/100m	45.8	45.8	35.2	35.2	37.7	34.7	25	100 ± 12	100 ± 10
25	10.3 dB/100m	44.3	44.3	34.1	34.1	35.8	32.8	24.3	100 ± 15	100 ± 10
31.25	11.6 dB/100m	42.9	42.9	31.3	31.3	33.9	30.9	23.6	100 ± 15	100 ± 10

62.5	16.8 dB/100m	38.4	38.4	21.6	21.6	27.8	24.8	21.5	100 ± 15	100 ± 10
100	21.7 dB/100m	35.3	35.3	17.1	17.1	23.8	20.8	20.1	100 ± 15	
155	27.7 dB/100m	32.5	32.5	4.7	4.7	19.9	16.9	19	100 ± 18	
200	32 dB/100m	30.8	30.8	3	3	17.7	14.7	19	100 ± 20	
250	36.4 dB/100m	29.3	29.3	0	0	15.8	12.8	18	100 ± 20	
300	40.5 dB/100m	28.2	28.2	0	0	14.2	11.2	18	100 ± 20	
310	41.3 dB/100m	27.9	27.9			13.9	10.9	18	100 ± 20	
350	44.3 dB/100m	27.2	27.2			12.9	9.9	17	100 ± 22	

Voltage

UL Voltage Rating
300 V (PLTC, CMR/CMX-Outdoor), 600 V (AWM)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation	Storage
60°C	-25°C To +75°C	-10°C To +75°C	-25°C To +75°C

Bend Radius

Stationary Min.
1.2 in (30 mm)

Max. Pull Tension:	40 lbs (18 kg)
Bulk Cable Weight:	42 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance, Oil Resistance
Flammability / Reaction to Fire:	UL1666 Riser, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, Article 725, CMR, CMX-Outdoor, PLTC
AWM Compliance:	AWM 21047
CEC / C(UL) Compliance:	CMR.
Data Category:	Category 5e
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 5e
Third Party Performance Verification:	Category 5e
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-5
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Operating temperatures are subject to length de-rating
--------	--

History

Update and Revision:	Revision Number: 0.657 Revision Date: 02-20-2026
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
7922A 0101000	Black	Reel	1,000 ft	612825191292	C
7922A 0102000	Black	Reel	2,000 ft	612825191308	C
7922A 0105000	Black	Reel	5,000 ft	612825191315	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.