




PART NO.	DRIVER ASM	INPUT CURRENT MAX.	OUTPUT CURRENT MAX.	OUTPUT POWER MAX.	STATUS
180996-1004	SINGLE CHANNEL	900mA	1050mA	42W	ACTIVE
180996-1007	SINGLE CHANNEL	260mA	300mA	13W	ACTIVE

SINGLE DRIVER ASSEMBLY OFFSET MOUNT






TABS FOR MOUNTING
DRIVER VERTICAL



TABS FOR MOUNTING
DRIVER HORIZONTAL

ETL LABEL



ISO VIEW

107.95
[4.25]
MOUNTING FOR VERTICAL DRIVER
MOUNTING HOLE LOCATION
HOLES FOR A #6-32 SELF TAPPING SCREW

19.05
[.75]
107.95
[4.25]
MOUNTING FOR HORIZONTAL DRIVER
MOUNTING HOLE LOCATION
HOLES FOR A #6-32 SELF TAPPING SCREW


- NOTES:
- HOUSING EXTRUSION
MATERIAL: ANODIZED ALUMINUM
 - STAMPED END CAP LEFT & RIGHT
MATERIAL: ALUMINUM
FINISH: TEXTURED POWDER COAT, BLACK

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
DIVISIONAL SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex DRIVER ASSEMBLY SINGLE/DUAL CHANNEL					
		MM/INCH		NTS												
		GENERAL TOLERANCES (UNLESS SPECIFIED)														
				MM		INCH	EC NO: 700562 DRWN: UKOWSHIKARAN 2022/03/22 CHK'D: RCG 2022/03/28 APPR: RCG 2022/03/28					PRODUCT CUSTOMER DRAWING				
		4 PLACES		±		±										
		3 PLACES		±		±										
		2 PLACES		±	0.25	± 0.01										
		1 PLACE		±	0.5	± 0.02										
		0 PLACES		±		±	INITIAL REVISION: DRWN: GALLENO2 2017/12/03 APPR: JAGRO 2018/10/12					DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
		ANGULAR TOL		±	°	1809960000						PSD	000	B		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER			
							A1-SIZE	180996	SEE TABLE		GENERAL MARKET		1 OF 7			


DOCUMENT STATUS	P1	RELEASE DATE	2022/03/28	18:00:12
-----------------	----	--------------	------------	----------

PART NO.	DRIVER ASM	INPUT CURRENT MAX.	OUTPUT CURRENT MAX.	OUTPUT POWER MAX.	STATUS
180996-2001	DUAL CHANNEL	300mA	350mA	14W	ACTIVE
180996-2002	DUAL CHANNEL	430mA	500mA	20W	ACTIVE
180996-2003	DUAL CHANNEL	600mA	700mA	28W	ACTIVE
180996-2004	DUAL CHANNEL	900mA	1050mA	42W	ACTIVE
180996-2006	DUAL CHANNEL	750mA	880mA	35W	ACTIVE

DUAL DRIVER ASSEMBLY OFFSET MOUNT








TABS FOR MOUNTING
DRIVER VERTICAL



ETL LABEL

TABS FOR MOUNTING
DRIVER HORIZONTAL










ISO VIEW

- NOTES:
- HOUSING EXTRUSION
MATERIAL: ANODIZED ALUMINUM
 - STAMPED END CAP LEFT & RIGHT
MATERIAL: ALUMINUM
FINISH: TEXTURED POWDER COAT, BLACK

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
E/A = 0		DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex									
		MM/INCH		NTS															
E/C = 0		GENERAL TOLERANCES (UNLESS SPECIFIED)																	
E/P = 0				MM	INCH					EC NO: 700562 DRWN: UKOWSHIKARAN CHK'D: RCG APPR: RCG 2022/03/22 2022/03/28 2022/03/28				DRIVER ASSEMBLY SINGLE/DUAL CHANNEL					
		4 PLACES		±	±														
DIVISIONAL SYMBOLS		3 PLACES		±	±														
		2 PLACES		±	0.25	±	0.01												
		1 PLACE		±	0.5	±	0.02												
		0 PLACES		±	±														
		ANGULAR TOL		±	°														
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
								A1-SIZE		180996		1809960000		PSD		000		B	
												MATERIAL NUMBER		CUSTOMER				SHEET NUMBER	
												SEE TABLE		GENERAL MARKET				2 OF 7	

PART NO.	DRIVER ASM	INPUT CURRENT MAX.	OUTPUT CURRENT MAX.	OUTPUT POWER MAX.	STATUS
180996-3104	SINGLE CHANNEL	900mA	1050mA	42W	ACTIVE
180996-3107	SINGLE CHANNEL	260mA	300mA	13W	ACTIVE

SINGLE DRIVER ASSEMBLY CENTER MOUNT










- NOTES:
- 1. HOUSING EXTRUSION
MATERIAL: ANODIZED ALUMINUM
 - 2. STAMPED END CAP LEFT & RIGHT
MATERIAL: ALUMINUM
FINISH: TEXTURED POWDER COAT, BLACK

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																				
FA = 0 FC = 0 FP = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:						molex											
	MM/INCH		NTS																			
	GENERAL TOLERANCES (UNLESS SPECIFIED)																					
		MM		INCH							EC NO: 700562 DRWN: UKOWSHIKARAN 2022/03/22 CHK'D: RCG 2022/03/28 APPR: RCG 2022/03/28						DRIVER ASSEMBLY SINGLE/DUAL CHANNEL					
4 PLACES		±		±																		
3 PLACES		±		±																		
2 PLACES		±	0.25	± 0.01													PRODUCT CUSTOMER DRAWING					
1 PLACE		±	0.5	± 0.02																		
0 PLACES		±		±																		
DIVISIONAL SYMBOLS	ANGULAR TOL				±	°	INITIAL REVISION:				DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION					
	DRWN: GALEEN02				2017/12/12				1809960000		PSD		000		B							
	APPR: JAGRO				2018/10/03																	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION				DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER					
									A1-SIZE		180996		SEE TABLE		GENERAL MARKET		3 OF 7					

DOCUMENT STATUS	P1	RELEASE DATE	2022/03/28	18:00:12
-----------------	----	--------------	------------	----------

PART NO.	DRIVER ASM	INPUT CURRENT MAX.	OUTPUT CURRENT MAX.	OUTPUT POWER MAX.	STATUS
180996-4101	DUAL CHANNEL	300mA	350mA	14W	ACTIVE
180996-4103	DUAL CHANNEL	600mA	700mA	28W	ACTIVE
180996-4104	DUAL CHANNEL	900mA	1050mA	42W	ACTIVE
180996-4106	DUAL CHANNEL	750mA	880mA	35W	ACTIVE

DUAL DRIVER ASSEMBLY CENTER MOUNT



ISO VIEW




- NOTES:
- 1. HOUSING EXTRUSION
MATERIAL: ANODIZED ALUMINUM
 - 2. STAMPED END CAP LEFT & RIGHT
MATERIAL: ALUMINUM
FINISH: TEXTURED POWDER COAT, BLACK

DOCUMENT STATUS	P1	RELEASE DATE	2022/03/28	18:00:12
-----------------	----	--------------	------------	----------



FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
FA = 0 FC = 0 FP = 0 DIVISIONAL SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC:					molex DRIVER ASSEMBLY SINGLE/DUAL CHANNEL							
		MM/INCH		NTS														
		GENERAL TOLERANCES (UNLESS SPECIFIED)																
				MM		INCH		EC NO: 700562 DRWN: UKOWSHIKARAN 2022/03/22 CHK'D: RCG 2022/03/28 APPR: RCG 2022/03/28 INITIAL REVISION: DRWN: GALLEN02 2017/12/12 APPR: JAGRO 2018/10/03					PRODUCT CUSTOMER DRAWING					
		4 PLACES		±		±							DOCUMENT NUMBER		DOC TYPE		DOC PART	
3 PLACES		±		±		1809960000							PSD		000		B	
		2 PLACES		± 0.25		± 0.01												
		1 PLACE		± 0.5		± 0.02												
		0 PLACES		±		±												
		ANGULAR TOL				± °												
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER		
								D-SIZE		180996		SEE TABLE		GENERAL MARKET		4 OF 7		

PART NO.	DRIVER ASM	INPUT CURRENT MAX.	OUTPUT CURRENT MAX.	OUTPUT POWER MAX.	STATUS
180996-5101	SINGLE CHANNEL	300mA	350mA	14W	ACTIVE
180996-5102	SINGLE CHANNEL	430mA	500mA	20W	ACTIVE
180996-5103	SINGLE CHANNEL	600mA	700mA	28W	ACTIVE
180996-5104	SINGLE CHANNEL	900mA	1050mA	42W	ACTIVE
180996-5106	SINGLE CHANNEL	750mA	880mA	35W	ACTIVE
180996-5107	SINGLE CHANNEL	260mA	300mA	13W	ACTIVE
180996-5108	SINGLE CHANNEL	1025mA	1200mA	51W	ACTIVE
180996-5109	SINGLE CHANNEL	1200mA	1400mA	59W	ACTIVE

SINGLE DRIVER ASSEMBLY UNIVERSAL MOUNT






TABS FOR MOUNTING
DRIVER VERTICAL



ETL LABEL

TABS FOR MOUNTING
DRIVER HORIZONTAL



ISO VIEW

- NOTES:
- HOUSING EXTRUSION
MATERIAL: ANODIZED ALUMINUM
 - STAMPED END CAP LEFT & RIGHT
MATERIAL: ALUMINUM
FINISH: TEXTURED POWDER COAT, BLACK

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
FUNCTIONAL SYMBOLS E/A = 0 E/C = 0 E/P = 0 DIVISIONAL SYMBOLS	DIMENSION UNITS			SCALE		CURRENT REV DESC: EC NO: 700562 DRWN: UKOWSHIKARAN 2022/03/22 CHK'D: RCG 2022/03/28 APPR: RCG 2022/03/28 EC NO: 700562 DRWN: UKOWSHIKARAN 2022/03/22 CHK'D: RCG 2022/03/28 APPR: RCG 2022/03/28 INITIAL REVISION: DRWN: GALLEN02 2017/12/12 APPR: JAGRO 2018/10/03 THIRD ANGLE PROJECTION  DRAWING A1-SIZE SERIES 180996					molex				
	MM/INCH		NTS												
	GENERAL TOLERANCES (UNLESS SPECIFIED)										DRIVER ASSEMBLY SINGLE/DUAL CHANNEL				
		MM		INCH											
	4 PLACES		±		±										
	3 PLACES		±		±										
	2 PLACES		±	0.25	± 0.01										
	1 PLACE		±	0.5	± 0.02										
	0 PLACES		±		±										
	ANGULAR TOL		±	°											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					MATERIAL NUMBER SEE TABLE					CUSTOMER GENERAL MARKET		SHEET NUMBER 5 OF 7			

DOCUMENT STATUS	P1	RELEASE DATE	2022/03/28	18:00:12
-----------------	----	--------------	------------	----------

SINGLE OR DUAL)
E ORIENTATION
OR CoreSync LOGO)

MANUFACTURING/WAREHOUSE
LABEL (SEE NOTE 3)

CoreSync

molex

Output

Input

The diagram shows a large rectangular box labeled "MASTER PACK BOX" with an arrow pointing to its top surface. To the left of the box is a stack of 12 smaller rectangular boxes, arranged in a 3x4 grid. An arrow points from the text "MANUFACTURING/WAREHOUSE LABEL (SEE NOTE 3)" to a small rectangular label on the side of the Master Pack Box. Another arrow points from the top-left corner of the stack of smaller boxes towards the Master Pack Box.

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																					
$\frac{F}{A} = 0$ $\frac{F}{E} = 0$ $\frac{F}{E} = 0$		DIMENSION UNITS MM/INCH		SCALE NTS		CURRENT REV DESC: EC NO: 700562 DRWN: UKOWSHIKARAN 2022/03/22 CHK'D: RCG 2022/03/28 APPR: RCG 2022/03/28		molex DRIVER ASSEMBLY SINGLE/DUAL CHANNEL																															
DIVISIONAL SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		<table border="1"> <tr> <td></td> <td>MM</td> <td>INCH</td> </tr> <tr> <td>4 PLACES</td> <td>±</td> <td>±</td> </tr> <tr> <td>3 PLACES</td> <td>±</td> <td>±</td> </tr> <tr> <td>2 PLACES</td> <td>± 0.25</td> <td>± 0.01</td> </tr> <tr> <td>1 PLACE</td> <td>± 0.5</td> <td>± 0.02</td> </tr> <tr> <td>0 PLACES</td> <td>±</td> <td>±</td> </tr> <tr> <td colspan="2">ANGULAR TOL</td> <td>±</td> <td>°</td> </tr> </table>									MM	INCH	4 PLACES	±	±	3 PLACES	±	±	2 PLACES	± 0.25	± 0.01	1 PLACE	± 0.5	± 0.02	0 PLACES	±	±	ANGULAR TOL		±	°	PRODUCT CUSTOMER DRAWING <table border="1"> <tr> <td>DOCUMENT NUMBER</td> <td>DOC TYPE</td> <td>DOC PART</td> <td>REVISION</td> </tr> <tr> <td>1809960000</td> <td>PSD</td> <td>000</td> <td>B</td> </tr> </table>		DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
					MM			INCH																															
				4 PLACES	±			±																															
		3 PLACES	±	±																																			
2 PLACES	± 0.25	± 0.01																																					
1 PLACE	± 0.5	± 0.02																																					
0 PLACES	±	±																																					
ANGULAR TOL		±	°																																				
DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION																																				
1809960000	PSD	000	B																																				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION 		DRAWING A1-SIZE		SERIES 180996		MATERIAL NUMBER SEE TABLE		CUSTOMER GENERAL MARKET		SHEET NUMBER 7 OF 7																											

DOCUMENT STATUS	P1	RELEASE DATE	2022/03/28	18:00:12
-----------------	----	--------------	------------	----------