

# Bundling and Securing

## Cable Ties


### Standard Cable Ties

#### T18R and T30R Series in Colors

T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

#### Features and Benefits

- Engineered and manufactured for maximum performance and quality.
- Made from 100% high-quality plastic to ensure efficient recycling.
- Inside serration for a strong grip onto bundles.
- Easy application either manually or with a tensioning tool.
- Bent tail allows for simpler insertion.



| PART NO.  | TYPE | Min. Tensile Strength lbs. (N) | Length (L) in. (mm) | Max. Bundle Diameter in. (mm) | Width (W) in. (mm) | Material | Color  | Pkg. Qty. |
|-----------|------|--------------------------------|---------------------|-------------------------------|--------------------|----------|--------|-----------|
| 116-01816 | T18R | 18.0 (80.0)                    | 4.0 (100.0)         | 0.9 (22.0)                    | 0.1 (2.5)          | PA66     | Blue   | 100       |
| T18R6M4*  |      | 18.0 (80.0)                    | 4.0 (100.0)         | 0.9 (22.0)                    | 0.1 (2.5)          | PA66     | Blue   | 1000      |
| 111-01933 |      | 18.0 (80.0)                    | 4.0 (100.0)         | 0.9 (22.0)                    | 0.1 (2.5)          | PA66     | Brown  | 100       |
| T18R1M4*  |      | 18.0 (80.0)                    | 4.0 (100.0)         | 0.9 (22.0)                    | 0.1 (2.5)          | PA66     | Brown  | 1000      |
| 116-01818 |      | 18.0 (80.0)                    | 4.0 (100.0)         | 0.9 (22.0)                    | 0.1 (2.5)          | PA66     | Gray   | 100       |
| T18R8M4*  |      | 18.0 (80.0)                    | 4.0 (100.0)         | 0.9 (22.0)                    | 0.1 (2.5)          | PA66     | Gray   | 1000      |
| 116-01815 |      | 18.0 (80.0)                    | 4.0 (100.0)         | 0.9 (22.0)                    | 0.1 (2.5)          | PA66     | Green  | 100       |
| T18R5M4*  |      | 18.0 (80.0)                    | 4.0 (100.0)         | 0.9 (22.0)                    | 0.1 (2.5)          | PA66     | Green  | 1000      |
| 111-01934 |      | 18.0 (80.0)                    | 4.0 (100.0)         | 0.9 (22.0)                    | 0.1 (2.5)          | PA66     | Orange | 100       |
| T18R3M4*  |      | 18.0 (80.0)                    | 4.0 (100.0)         | 0.9 (22.0)                    | 0.1 (2.5)          | PA66     | Orange | 1000      |
| T18R7M4*  |      | 18.0 (80.0)                    | 4.0 (100.0)         | 0.9 (22.0)                    | 0.1 (2.5)          | PA66     | Purple | 1000      |
| 116-01812 |      | 18.0 (80.0)                    | 4.0 (100.0)         | 0.9 (22.0)                    | 0.1 (2.5)          | PA66     | Red    | 100       |
| T18R2M4*  |      | 18.0 (80.0)                    | 4.0 (100.0)         | 0.9 (22.0)                    | 0.1 (2.5)          | PA66     | Red    | 1000      |
| 111-01935 |      | 18.0 (80.0)                    | 4.0 (100.0)         | 0.9 (22.0)                    | 0.1 (2.5)          | PA66     | Violet | 100       |
| 111-01936 |      | 18.0 (80.0)                    | 4.0 (100.0)         | 0.9 (22.0)                    | 0.1 (2.5)          | PA66     | White  | 100       |
| T18R10M4* |      | 18.0 (80.0)                    | 4.0 (100.0)         | 0.9 (22.0)                    | 0.1 (2.5)          | PA66     | White  | 1000      |
| 116-01814 |      | 18.0 (80.0)                    | 4.0 (100.0)         | 0.9 (22.0)                    | 0.1 (2.5)          | PA66     | Yellow | 100       |
| T18R4M4*  |      | 18.0 (80.0)                    | 4.0 (100.0)         | 0.9 (22.0)                    | 0.1 (2.5)          | PA66     | Yellow | 1000      |

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes. Installation tools: EVO7 and EVO7SP. \*This product meets UL standards. Please see appendix for specific file numbers.



Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.