

Cable Ties in Special Materials


UV Stabilized Cable Ties

Used in the solar industry and other applications, HellermannTyton offers cable ties made of UV stabilized PA66UV material. This material provides additional protection against UV radiation for long-term outdoor use and is available in various styles, tensile strengths, and bundle diameters. T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.



Features and Benefits

- UV stabilized cable ties are designed for extended use outdoors.
- Inside serrations provide strong grip on cables and wire bundles.
- Easy application either manually or with a tensioning tool.
- Bent tail ensures a quick and simple installation.



PART NO.	TYPE	Min. Tensile Strength lbs. (N)	Length (L) in. (mm)	Max. Bundle Diameter in. (mm)	Width (W) in. (mm)	Material	Color	Pkg. Qty.
T18R0UVM4*	T18R	18.0 (80.0)	4.0 (100.0)	0.9 (22.0)	0.1 (2.5)	PA66UV	Black	1000
T18R0UVC2*		18.0 (80.0)	4.0 (100.0)	0.9 (22.0)	0.1 (2.5)	PA66UV	Black	100
T30R0UVM4*	T30R	30.0 (135.0)	5.8 (148.0)	1.4 (35.0)	0.1 (3.6)	PA66UV	Black	1000
T30R0UVC2*		30.0 (135.0)	5.8 (148.0)	1.4 (35.0)	0.1 (3.6)	PA66UV	Black	100
T30L0UVM4*	T30L	30.0 (135.0)	7.8 (198.0)	2.0 (50.8)	0.1 (3.6)	PA66UV	Black	1000
T30L0UVC2*		30.0 (135.0)	7.8 (198.0)	2.0 (50.8)	0.1 (3.6)	PA66UV	Black	100
T50R0UVM4*	T50R	50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	0.2 (4.6)	PA66UV	Black	1000
T50R0UVC2*		50.0 (225.0)	8.0 (202.0)	2.0 (50.0)	0.2 (4.6)	PA66UV	Black	100
T50I0UVC2*	T50I	50.0 (225.0)	12.0 (305.0)	3.2 (81.3)	0.2 (4.6)	PA66UV	Black	100
T50I0UVM4*		50.0 (225.0)	12.0 (305.0)	3.2 (81.3)	0.2 (4.6)	PA66UV	Black	1000
T50L0UVM4*	T50L	50.0 (225.0)	15.4 (390.0)	4.3 (109.2)	0.2 (4.8)	PA66UV	Black	1000
T50L0UVC2*		50.0 (225.0)	15.4 (390.0)	4.3 (109.2)	0.2 (4.8)	PA66UV	Black	100
T120S0UVK2*	T120S	120.0 (535.0)	8.9 (225.0)	2.2 (55.9)	0.3 (7.6)	PA66UV	Black	50
T120I0UVK2*	T120I	120.0 (535.0)	11.8 (300.0)	3.2 (81.3)	0.3 (7.6)	PA66UV	Black	50
T120R0UVH4*	T120R	120.0 (535.0)	15.2 (387.0)	4.1 (104.1)	0.3 (7.6)	PA66UV	Black	500
T120R0UVC2*		120.0 (535.0)	15.2 (387.0)	4.1 (104.1)	0.3 (7.6)	PA66UV	Black	100
T120L0UVK2*	T120L	120.0 (535.0)	30.0 (760.0)	8.9 (224.8)	0.3 (7.6)	PA66UV	Black	50

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.

Installation tools: EVO7, EVO7SP, EVO9, EVO9HT, MK7P, MK7HT, MK9P. *This product meets UL standards. Please see appendix for specific file numbers.

Bundling and Securing

Cable Ties

Cable Ties in Special Materials

UV Stabilized Cable Ties

PART NO.	TYPE	Min. Tensile Strength lbs. (N)	Length (L) in. (mm)	Max. Bundle Diameter in. (mm)	Width (W) in. (mm)	Material	Color	Pkg. Qty.
T150R0UVX2*	T150R(U)	175.0 (780.0)	15.4 (390.0)	4.1 (104.1)	0.4 (8.9)	PA66UV	Black	25
T150M0UVX2*	T150M	175.0 (780.0)	21.0 (530.0)	5.9 (150.0)	0.4 (8.9)	PA66UV	Black	25
T150L0UVX2*	T150L	175.0 (780.0)	32.3 (820.0)	9.6 (243.8)	0.4 (8.9)	PA66UV	Black	25
T150LL0UVX2*	T150LL	175.0 (780.0)	36.4 (925.0)	10.8 (274.3)	0.4 (8.9)	PA66UV	Black	25
T150XL0UVX2*	T150XL	175.0 (780.0)	43.1 (1,095.0)	13.0 (330.2)	0.4 (8.9)	PA66UV	Black	25
T150XLL0UVX2*	T150XLL	175.0 (780.0)	52.2 (1,325.0)	16.0 (406.4)	0.4 (8.9)	PA66UV	Black	25
111-00925*	T250M	250.0 (1,115.0)	22.3 (565.3)	5.9 (150.0)	0.5 (12.4)	PA66UV	Black	25

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.

Installation tools: EVO7, EVO7SP, EVO9, EVO9HT, MK7P, MK7HT, MK9P. *This product meets UL standards. Please see appendix for specific file numbers.



Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.