



Sample Kit 1009

TDK Part #	Case Size	Temperature Coefficient	Voltage (DC)	Value	Tolerance Code	Tolerance Value	Thickness
<a href="#">C0603COG1E0R2W</a>	0603	C0G	25	0.2pF	W	+/-0.05pF	0.30
<a href="#">C0603COG1E0R3W</a>	0603	C0G	25	0.3pF	W	+/-0.05pF	0.30
<a href="#">C0603COG1E0R4W</a>	0603	C0G	25	0.4pF	W	+/-0.05pF	0.30
<a href="#">C0603COG1E0R5W</a>	0603	C0G	25	0.5pF	W	+/-0.05pF	0.30
<a href="#">C0603COG1E0R6W</a>	0603	C0G	25	0.6pF	W	+/-0.05pF	0.30
<a href="#">C0603COG1E0R7W</a>	0603	C0G	25	0.7pF	W	+/-0.05pF	0.30
<a href="#">C0603COG1E0R75B</a>	0603	C0G	25	0.75pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E0R8W</a>	0603	C0G	25	0.8pF	W	+/-0.05pF	0.30
<a href="#">C0603COG1E0R9W</a>	0603	C0G	25	0.9pF	W	+/-0.05pF	0.30
<a href="#">C0603COG1E010B</a>	0603	C0G	25	1pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E1R1B</a>	0603	C0G	25	1.1pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E1R2B</a>	0603	C0G	25	1.2pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E1R3B</a>	0603	C0G	25	1.3pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E1R5B</a>	0603	C0G	25	1.5pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E1R6B</a>	0603	C0G	25	1.6pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E1R8B</a>	0603	C0G	25	1.8pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E020B</a>	0603	C0G	25	2pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E2R2B</a>	0603	C0G	25	2.2pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E2R4B</a>	0603	C0G	25	2.4pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E2R7B</a>	0603	C0G	25	2.7pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E030B</a>	0603	C0G	25	3pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E3R3B</a>	0603	C0G	25	3.3pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E3R6B</a>	0603	C0G	25	3.6pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E3R9B</a>	0603	C0G	25	3.9pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E040B</a>	0603	C0G	25	4pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E4R3B</a>	0603	C0G	25	4.3pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E4R7B</a>	0603	C0G	25	4.7pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E050B</a>	0603	C0G	25	5pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E5R1B</a>	0603	C0G	25	5.1pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E5R6B</a>	0603	C0G	25	5.6pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E060B</a>	0603	C0G	25	6pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E6R2B</a>	0603	C0G	25	6.2pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E6R8B</a>	0603	C0G	25	6.8pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E070B</a>	0603	C0G	25	7pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E7R5B</a>	0603	C0G	25	7.5pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E080B</a>	0603	C0G	25	8pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E8R2B</a>	0603	C0G	25	8.2pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E090B</a>	0603	C0G	25	9pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E9R1B</a>	0603	C0G	25	9.1pF	B	+/-0.10pF	0.30
<a href="#">C0603COG1E100E</a>	0603	C0G	25	10pF	E	+/-0.20pF	0.30