



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	09APR2025	GC	JM

NOTES:
1.MATERIAL:
TERMINAL: PHOSPHOR BRONZE,T=0.12mm.

2.FINISH:
CONTACTS: GOLD FLASH ON SOLDERING AREA.

3.SPECIFICATION:
VOLTAGE RATING: 30V AC/DC
CURRENT RATING: 1 A


4.THE PRODUCT IS RoHS AND HF COMPLIANT





Part No	Wire Range	Insulation O.D.	Material	Finish	Qty/reel
2495756-1	AWG #28~#32	0.50~0.60	Phosphor Bronze	1u" AuOn Ni	20,000 pcs

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Gowtham 01OCT2024	TE Connectivity Ltd.		
DIMENSIONS: mm		CHK JAGRUTHI 01/10/2024			
		APVD GOWTHAM 01/10/2024	NAME -		
		PRODUCT SPEC 108-161611	0.8mm CRIMP RECEPTACLE WTB CONTACT		
MATERIAL -		APPLICATION SPEC 114-161208	SIZE A2	CAGE CODE 00779	DRAWING NO C=2495756
FINISH -		WEIGHT 0	RESTRICTED TO -		
		CUSTOMER DRAWING	SCALE 1:1	SHEET 1 of 2	REV A

REVISIONS					
P	LTR	DESCRIPTION	DATE	OWN	APVD
	-	SEE SHEET 1	-	-	-




TERMINAL




paper tray (Ø480mm)


adhesive tape




angle bead





Load carton



desiccant



Sealed carton



Part No	Qty/reel	Qty/Box
2495756-1	20000 PCS	80000 PCS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Gowtham CHK JAGRUTHI APVD GOWTHAM		01OCT2024 01/10/2024 01/10/2024		 TE Connectivity Ltd.								
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		- 0.8mm CRIMP RECEPTACLE WTB CONTACT -								
		0 PLC	±	-	PRODUCT SPEC		SIZE A2		CAGE CODE 00779		DRAWING NO C=2495756		RESTRICTED TO -	
		1 PLC	±	0.25	108-161611									
		2 PLC	±	0.15	APPLICATION SPEC									
		3 PLC	±	0.08	114-161208		SCALE		SHEET		REV			
		4 PLC	±	-	WEIGHT		1:1		2 of 2		A			
MATERIAL -		FINISH -		0		CUSTOMER DRAWING								