


## Cable Ties in Special Materials

### ETFE Cable Ties

ETFE ties provide excellent protection against radiation, ultraviolet light, and a wide range of chemicals. They are also rated for low outgassing applications. HellermannTyton's ETFE ties come in a standard color of blue for easy identification. T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

### Features and Benefits

- ETFE cable ties provide excellent resistance to chemicals, radiation, high temperatures and UV exposure.
- Inside serrations allows for strong grip on cables and wire bundles.
- Head design provides high tensile strength with very low insertion force.
- Bent tail ensures a quick and simple installation.



PART NO.	TYPE	Min. Tensile Strength lbs. (N)	Length (L) in. (mm)	Max. Bundle Diameter in. (mm)	Width (W) in. (mm)	Material	Color	Pkg. Qty.
111-00659*	T18R	18.0 (80.0)	4.0 (100.0)	0.9 (22.0)	0.1 (2.5)	E/TFE	Blue	100
111-00698*	T30R	30.0 (133.3)	6.0 (150.0)	1.4 (36.0)	0.1 (3.5)	E/TFE	Blue	100
111-00732*	T50R	50.0 (222.3)	8.0 (202.0)	2.0 (50.0)	0.2 (4.7)	E/TFE	Blue	100
111-00718*	T50L	50.0 (222.3)	15.0 (382.0)	4.1 (105.0)	0.2 (4.7)	E/TFE	Blue	100
111-01125*	T120R	120.0 (535.0)	15.2 (387.0)	4.1 (105.0)	0.3 (7.4)	E/TFE	Blue	50

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.

Installation tools: EVO7, EVO7SP, EVO9, EVO9HT, MK7P, MK7HT, MK9P. \*This product meets UL standards. Please see appendix for specific file numbers.



Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.