

HVAC Selection Guide

Protect and Control the Critical Components in Your HVAC Systems

LITTELFUSE PRODUCT & PART NUMBER	BENEFITS	FEATURES	COMPETITOR PART NUMBERS
FUSES, HOLDERS & DISTRIBUTION BLOCKS	Class CC & Midget Fuses CCMR, KLDR, KLKR, KLKD 	Provides extreme current-limitation in a space-saving design and are available up to 60 A.	<ul style="list-style-type: none"> Ideal for space saving protection High-interrupting capacity and excellent current-limitation
	Class R fuses FLNR, FLSR 	Ideal when cost is a major consideration, UL Class R fuses offer high reliability with their proven, mature design.	<ul style="list-style-type: none"> High short-circuit current rating Dual-element design Available with and without indication
	Class T Fuses JLLN, JLLS 	For sensitive electrical components, UL Class T fuses are ideal for places where space and protection are critical. They provide the protection of a Class R fuse but are approximately 1/3 of the size.	<ul style="list-style-type: none"> Extremely current-limiting 200 kA interrupting rating
	Class J Fuses JTD 	UL Class J fuses are critical for places where space is at a premium and maximum protection is an imperative. Providing the protection of a class RK1 fuse in a smaller footprint, these fuses can be used for a wider range of applications reducing inventory requirements.	<ul style="list-style-type: none"> Superior time-delay and cycling characteristics Available with and without indication
Littelfuse offers a wide variety of UL approved open face, finger safe, and panel mount fuse holders, as well as power distribution blocks. Visit the Littelfuse website to see our full offering.			
SURGE PROTECTION DEVICES (SPD)	Type 2 Surge Protection Devices SPD 	Safeguards components from power fluctuations or surges by limiting the fault current to a load or the unit being protected to prevent equipment damage or downtime.	<ul style="list-style-type: none"> Capability to clamp and withstand high-energy transients to prevent disruption, downtime, and degradation or damage to equipment Thermal protection to eliminate catastrophic failure UL Recognized and IEC Compliant in one part number to reduce inventory and support global usage DIN-rail mounted and compact footprint to increase panel design flexibility An SPD type and voltage-coded plug to prevent module from being placed in wrong base, eliminating the risk of improper protection
OVERLOAD RELAY	Enhanced Overload Relay MP8000 	Provides advanced motor protection and is fully programmable via Bluetooth* using the Littelfuse app on an Android* or iOS* mobile device.	<ul style="list-style-type: none"> Programmable voltage and current settings 3 selectable restart options 4 programmable delay timers Programmable auxiliary relay output
Contact Littelfuse for more information			

*Bluetooth, Android, and iOS are trademarks of their respective owners.

HVAC Selection Guide

Protect and Control the Critical Components in Your HVAC Systems

LITTELFUSE PRODUCT & PART NUMBER	BENEFITS	FEATURES	COMPETITOR PART NUMBERS
VOLTAGE & PHASE MONITORS	Three-Phase Voltage Monitors 460 	Protects compressors and blower motors from adverse voltage conditions that can cause damage to the motor windings.	<ul style="list-style-type: none"> Universal range from 190 to 480 V ac or 475 to 600 V ac and 50/60 Hz Transient protection meets IEEE and IEC standards Four adjustment pots provide versatility for a variety of applications Adjustable trip delay and restart delay Standard surface or DIN-rail mountable <p>Diversified: SLU100ASD Time Mark: Series 158 ICM Controls: ICM 401 up to 480 V ac Macromatic: PMDU Agastat: PMA series Crouzet: UFR2 series Electronics: PVC400AR</p>
	Three-Phase Voltage Monitors 250A 	Protects compressors and blower motors from adverse voltage conditions that can cause damage to the motor windings.	<ul style="list-style-type: none"> Protection from low and high voltage, unbalance, single-phase, and reverse-phase conditions LED diagnostics is quick visual indicator for cause of trip Adjustable trip delay to prevent nuisance tripping DPDT relay output <p>A-1 Components: EAC-800 series Diversified: SLA,* SLC,* SLM* R-K Electronics: PVCL Time Mark: Series 2642, 2644 WatSCO: EAC-800</p> <p>*If 2 Form C contacts are required, SLJ-XXX-ALE</p>
	Three-Phase Voltage Monitors 455 	Provides all the same voltage/phase protection as the 460 model, but with three added advantages listed in the features section.	<ul style="list-style-type: none"> Second set of voltage inputs for monitoring voltage on the load-side of the motor contactor to detect contact failure Keeps history of the past 20 fault causes Wirelessly download and view fault history <p>ICM Controls: ICM450, ICM400 A-1 Components: EAC-8001 WatSCO: EAC-8001</p>
	Three-Phase Voltage Monitors 201A 	Protects compressors and blower motors from adverse voltage conditions that can cause damage to the motor windings regardless of size.	<ul style="list-style-type: none"> Protection for low voltage, voltage unbalance, phase reversal, and harmful power line conditions. Optional high-voltage monitoring <p>Time Mark: 253, 257B Macromatic: PMPU-FA8</p>
Other available voltage monitors commonly used for HVAC applications are 201A-9, 460, 460-575, 460-14, 250A, 202, 455, and 460-200-SP			
CURRENT MONITORING RELAYS	Self-Powered GO/NO GO Ac Current Sensors LSRX-C, LSRX 	Energizes the output contact whenever 4.5 amps or greater is present. Used commonly as an ac current proof relay to indicate if a motor is operating.	<ul style="list-style-type: none"> Self-powered Quick-connect terminals reduce installation time Built-in current sensor eliminates the need for a stand alone current transformer <p>Diversified: CMG-0100-20, CMG-0100-24, CMG-0100-28, CMG-0100-32, CMG-0100-36, CMG-0200-20, CMG-0200-24, CMG-0200-28, CMG-0200-32, CMG-0200-36</p>
	Ac Current Transducers TCSA20 	Varies the effective resistance of its output in direct proportion to the current flowing in the conductor it is monitoring.	<ul style="list-style-type: none"> Monitors 0 to 20 A Loop powered from 10 to 30 V dc Linear output from 4 to 20 mA <p>AcuAMP: ACT050-42L-S (split core 0 to 50 A) Hawkeye: H721HC (0 to 30 A)</p>
Other available ac current transducers commonly used for HVAC applications are TCSA5, TCSA10, TCSA50			

LITTELFUSE PRODUCT & PART NUMBER				BENEFITS	FEATURES	COMPETITOR PART NUMBERS
TIME DELAY RELAYS	Delay-on-Make Timers ¹ TMV8000		Delay the blower from turning on, to allow time for the system to reach temperature before forcing air through the ventilation ducts. Also used to stagger start for multiple compressors within a facility, on start up or after a power outage.	<ul style="list-style-type: none"> Universal ac/dc operating voltage Two terminal series connection with the load Solid state prevents arc and wear over time Encapsulated to protect against shock vibration 	Macromatic: THL-1024U-32 Ametek NCC: O1T-00600-311 Diversified and Time Mark: Several (contact technical support)	
	Delay-on-Break Timers ² TDUB3000A		Used to delay the blower from turning off, after the demand has been met to allow all of the conditioned air to be forced out of the ventilation ducts.	<ul style="list-style-type: none"> 24 to 120 V ac input voltage User selectable time delay Solid state prevents arc and wear over time Encapsulated to protect against shock vibration 	Macromatic: THR-11662-31T, POM Airotronics: TGML10100A1	
	HVAC-R Timers CT1S45		Combines a delay-on-make and delay-on-break time delay into one unit and may be used to control fan delays in heating and/or cooling equipment.	<ul style="list-style-type: none"> Delay-on-make and delay-on-break in one unit Voltage 24 V ac input voltage Solid state prevents arc and wear over time Encapsulated to protect against shock vibration 	Can replace several competitors' delay-on-make and delay-on-break dual-function HVAC timers (contact technical support).	
	Multifunction Timers TRU1, TRU2 & TRU3		A multifunction universal time-delay relay. Six timing functions include delay-on-make, interval, single shot, recycling (ON time first, equal recycle delays), delay-on-break, and retriggerable single shot.	<ul style="list-style-type: none"> Universal input voltage Knob adjustable time delay LED indicators provide visual indication of input voltage and relay status 	TRU2: Diversified: All series of TBD, TBE, TUD-120-AKA, TUE-120-AFA, TUE-120-A Macromatic: TD-7, TD-8	
	Leaded Discrete, Surface Mount Discrete, Probes & Assemblies NTC Thermistors		Cost-effective, predictable temperature sensor that enables tighter operating control and diagnostics to achieve energy savings and optimal performance of systems.	<ul style="list-style-type: none"> Exponential resistance-temperature curve Wide operating temperature ranges from -50 °C to 300 °C Metal oxide ceramic compounds 	Contact Littelfuse for more information	
TEMPERATURE SENSORS	Leaded Discrete, Probes & Assemblies RTDs		Robust, extremely stable and predictable temperature sensor suitable for a wide range of temperatures that enables tighter operating control and diagnostics to achieve energy savings and optimal performance of systems.	<ul style="list-style-type: none"> Nearly linear resistance-temperature curve provides ease and consistency of measurement Extremely wide temperature ranges, specifically on the higher end, from -50 °C to well above 500 °C Precious metal (typically Pt) on ceramic substrate 	Contact Littelfuse for more information	

¹ Delay-on-Make Timer: Upon application of input voltage, the time delay (t) begins. The output is de-energized before and during the time delay, but then becomes energized at the end of the time delay (t).

² Delay-on-Break Timer: Once input voltage is applied, the time delay relay is ready to be activated. When the relay is activated, the output is energized. Then when the relay is deactivated, the time delay begins and the output remains energized during timing. At the end of the time delay, the output becomes de-energized.

This tool is intended to be used as a guide only. Check our cross reference document for a full list of competitor products substitutable with Littelfuse Class CC, RK5 & Class T Fuses. The user will need to verify the part is appropriate for the application. Contact our technical support team at 1-800-TEC-FUSE (1-800-832-3873) or techline@littelfuse.com.

Notes

Disclaimer Notice – Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/product-disclaimer.