



Sample Kit 1008

TDK Part #	Case Size	Temperature Coefficient	Voltage (DC)	Value	Tolerance Code	Tolerance Value	Thickness
C1608C0G2A101J	1608	C0G	100	100pF	J	+/-5%	0.80
C1608C0G2A102J	1608	C0G	100	1000pF	J	+/-5%	0.80
C1608C0G2E101J	1608	C0G	250	100pF	J	+/-5%	0.80
C2012C0G2A101J	2012	C0G	100	100pF	J	+/-5%	0.60
C2012C0G2A102J	2012	C0G	100	1000pF	J	+/-5%	0.60
C2012C0G2E101J	2012	C0G	250	100pF	J	+/-5%	0.60
C2012C0G2E102J	2012	C0G	250	1000pF	J	+/-5%	0.85
C3216C0G2A103J	3216	C0G	100	0.01uF	J	+/-5%	1.15
C3216C0G2J101J	3216	C0G	630	100pF	J	+/-5%	0.60
C3216C0G2J102J	3216	C0G	630	1000pF	J	+/-5%	0.85
C3225C0G2E103J	3225	C0G	250	0.01uF	J	+/-5%	1.60
C4532C0G2A104J	4532	C0G	100	0.1uF	J	+/-5%	3.20
C4532C0G2J103J	4532	C0G	630	0.01uF	J	+/-5%	1.60
C1005X7S2A102K	1005	X7S	100	1000pF	K	+/-10%	0.50
C1005X7S2A103K	1005	X7S	100	0.01uF	K	+/-10%	0.50
C1608X7R2A102K	1608	X7R	100	1000pF	K	+/-10%	0.80
C1608X7R2A103K	1608	X7R	100	0.01uF	K	+/-10%	0.80
C1608X7S2A104K	1608	X7S	100	0.1uF	K	+/-10%	0.80
C2012X7R2A102K	2012	X7R	100	1000pF	K	+/-10%	0.85
C2012X7R2A103K	2012	X7R	100	0.01uF	K	+/-10%	0.85
C2012X7R2A104K	2012	X7R	100	0.1uF	K	+/-10%	1.25
C2012X7R2E102K	2012	X7R	250	1000pF	K	+/-10%	0.85
C2012X7R2E103K	2012	X7R	250	0.01uF	K	+/-10%	1.25
C2012X7S2A105K	2012	X7S	100	1uF	K	+/-10%	1.25
C2012X7T2E104K	2012	X7T	250	0.1uF	K	+/-10%	1.25
C2012X7T2W103K	2012	X7T	450	0.01uF	K	+/-10%	0.85
C3216X7R2A104K	3216	X7R	100	0.1uF	K	+/-10%	1.60
C3216X7R2A105K	3216	X7R	100	1uF	K	+/-10%	1.60
C3216X7R2E104K	3216	X7R	250	0.1uF	K	+/-10%	1.60
C3216X7R2J102K	3216	X7R	630	1000pF	K	+/-10%	1.15
C3216X7R2J103K	3216	X7R	630	0.01uF	K	+/-10%	1.15
C3216X7T2W104K	3216	X7T	450	0.1uF	K	+/-10%	1.60
C3216X7T2J103K	3216	X7T	630	0.01uF	K	+/-10%	0.85
C3225X7R2A105K	3225	X7R	100	1uF	K	+/-10%	2.00
C3225X7R2E104K	3225	X7R	250	0.1uF	K	+/-10%	2.00
C3225X7T2J104K	3225	X7T	630	0.1uF	K	+/-10%	1.60
C4532X7R2A105K	4532	X7R	100	1uF	K	+/-10%	2.30
C4532X7R2J104K	4532	X7R	630	0.1uF	K	+/-10%	2.30
C4532X7T2E105K	4532	X7T	250	1uF	K	+/-10%	2.50
C5750X7R2A105K	5750	X7R	100	1uF	K	+/-10%	2.30
C5750X7R2E105K	5750	X7R	250	1uF	K	+/-10%	2.30
C5750X7S2A106M	5750	X7S	100	10uF	M	+/-20%	2.30
C5750X7T2W105K	5750	X7T	450	1uF	K	+/-10%	2.50